SIEMENS

Data sheet

6EP1935-6MD11



SITOP BATTERY MODULE/24V/3.2AH

SITOP battery module 24 V/3.2 Ah with maintenance-free sealed lead batteries for SITOP DC UPS module 6 A and 15 A *Ex approval no longer available*

Charging current charging voltage	
end-of-charge voltage at DC	
• at -10 °C recommended	29 V
 at 0 °C recommended 	28.4 V
 at 10 °C recommended 	27.8 V
 at 20 °C recommended 	27.3 V
 at 30 °C recommended 	26.8 V
 at 40 °C recommended 	26.6 V
 at 50 °C recommended 	26.3 V
Output	
charging current maximum	0.8 A
output voltage at DC rated value	24 V
Safety	
design of short-circuit protection	Battery fuse 15 A/32 V (solid-state circuitry blade-type fuse + support)
design of the overload protection	Valve control
Safety	
operating resource protection class	Class III
protection class IP	IP00
Approvals	
certificate of suitability	
CE marking	Yes
UL approval	Yes
 as approval for USA 	cURus-Recognized (UL 1778, CSA C22.2 No. 107.1), File E219627
 cCSAus, Class 1, Division 2 	No
• ATEX	No
certificate of suitability	
EAC approval	Yes
 shipbuilding approval 	Yes
shipbuilding approval	ABS, DNV GL
Marine classification association	
 American Bureau of Shipping Europe Ltd. (ABS) 	Yes
• DNV GL	Yes
environmental conditions	
Operating data note	For storage, mounting and operation of lead-acid batteries, the relevant DIN/VDE regulations or country-specific regulations (e.g. VDE 0510 Part 2/EN 50272-2) must be observed. You must ensure that the battery site is sufficiently ventilated. Possible sources of ignition must be at least 50 cm away.
ambient temperature	
during operation	-15 +50 °C
during transport	-20 +50 °C
during storage	-20 +50 °C

relative temporary capacity loss at 20 °C in a month typical	3 %
Service life	
service life of energy storage	
• typical	capacity falls to 80 % of original capacity (according to EUROBAT)
• at 20 °C typical	4 a
• at 30 °C typical	2 a
• at 40 °C typical	1 a
• at 50 °C typical	0.5 a
ambient temperature during storage	Along with the storage and operating temperature, other factors such as the duration of the storage period and the charge status during storage have a decisive influence on the possible useful life. Batteries should therefore be stored as briefly as possible, always fully charged, and within the temperature range 0 to +20 $^{\circ}$ C.
Mechanics	
type of electrical connection	spring-loaded terminals
 for power supply unit 	1 screw terminal each for 0.08 2.5 mm ² for + BAT and - BAT
product component included	Accessories pack with solid-state circuitry fuse 15 A
width of the enclosure	190 mm
height of the enclosure	151 mm
depth of the enclosure	82 mm
installation width	210 mm
mounting height	171 mm
fastening method	
wall mounting	Yes
 standard rail mounting 	Yes
S7 rail mounting	No
fastening method	snaps onto DIN rail EN 60715 35x7.5/15 or keyhole mounting for hooking in to M4 screws
net weight	3.2 kg
number of cells	12
battery capacity	3.2 A·h
other information	Specifications at rated input voltage and ambient temperature +25 $^\circ\text{C}$ (unless otherwise specified)

Ø