



HOSP GRD SGL RECEPT 20A 125V LA
Part No. 8301LA

- Heavy-Duty Hospital Grade Single Receptacle Back and Side-Wire 20A 125V

Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Impact-resistant nylon face and thermoplastic back body.

Internal screw-pressure-plate back wire capable of accepting #14 : #10 AWG solid or stranded copper or copper-clad wire.

Terminal compartments isolated from each other for positive conductor containment.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007091014
--------------	----------------	------------	--------------

Country Of Origin	Mexico
-------------------	--------

Listing Agencies / 3rd Party Agencies

cUL Listed	Yes
------------	-----