


# POWER DISTRIBUTION BLOCKS

Single Primary /  
Multiple Secondary

Blocks  
Snap  
Together  
Easily



LISTED



Part #	Temp Rating	Line Side	Load Side	Amps Per Pole	Insulator Block			Insulator Block Size (see chart on pg. D-63)
					Length	Width	Height	
ADB142/01	90°C	2/0-14	4-14AWG	175	2.90	1.04	2.34	S
ADB162/01	90°C	2/0-14	4-14AWG	175	2.90	1.04	2.34	S
ADB1623501	90°C	350MCM-6AWG	4-14AWG	310	4.00	1.71	2.62	M
ADB183501	90°C	350MCM-6AWG	4-14AWG	310	4.00	1.71	2.62	M
ADB1123501	90°C	350MCM-6AWG	4-14AWG	310	4.00	1.71	2.62	M
ADB1125001	90°C	500MCM-4AWG	4-14AWG	380	4.00	1.71	2.62	M
ADB145001	90°C	500MCM-4AWG	4/0-6AWG	380	5.50	2.90	3.25	L
ADB163501	90°C	350MCM-6AWG	2/0-14AWG	310	5.50	2.90	3.25	L
ADB165001	90°C	500MCM-4AWG	2/0-14AWG	380	5.50	2.90	3.25	L
ADB1610001	90°C	1000-250MCM AWG	2/0-14AWG	545	5.50	2.90	3.25	L

**COVERS (ONE COVER REQUIRED FOR EACH BLOCK ORDERED)**

CS\* S  
 CM M  
 CL L


\*FITS SIZE S MODULES EXCEPT ADB162/01, ADB222/01 & ADB2622/01

- 90°C rated
- 14 AWG to 1000 MCM
- Handles Copper and/or Aluminum wire
- Rated for use up to 600V
- High impact, extra strong bases

# POWER DISTRIBUTION BLOCKS

## Double Primary / Multiple Secondary

Blocks Snap Together Easily



LISTED



Part #	Temp Rating	Line Side	Load Side	Amps Per Pole	Insulator Block			Insulator Block Size (see chart on pg. D-63)
					Length	Width	Height	
ADB2622/01	90°C	2/0-14AWG	4-14AWG	350	2.90	1.04	2.34	S
ADB262/01	90°C	2/0-14AWG	4-14AWG	350	4.00	1.71	2.62	M
ADB282/01	90°C	2/0-14AWG	4-14AWG	350	4.00	1.71	2.62	M
ADB2122/01	90°C	2/0-14AWG	4-14AWG	350	4.00	1.71	2.62	M
ADB2632/01	90°C	2/0-14AWG	2-14AWG	350	4.00	1.71	2.62	M
ADB2123501	90°C	350MCM-6AWG	4-14AWG	620	5.50	2.90	3.25	L
ADB263501	90°C	350MCM-6AWG	2/0-14AWG	620	5.50	2.90	3.25	L
ADB2125001	90°C	500MCM-4AWG	4-14AWG	760	5.50	2.90	3.25	L
ADB265001	90°C	500MCM-4AWG	2/0-14AWG	760	5.50	2.90	3.25	L
ADB245001	90°C	500MCM-4AWG	4/0-6AWG	760	5.50	2.90	3.25	L

**COVERS (ONE COVER REQUIRED FOR EACH BLOCK ORDERED)**

CS\* S  
 CM M  
 CL L

\*FITS SIZE S MODULES EXCEPT ADB162/01, ADB222/01 & ADB2622/01



# SPLICER/REDUCERS

## Single Primary Multiple Secondary / Double Primary Multiple Secondary


Part #	Temp Rating	Line Side	Load Side	Amps Per Pole	Insulator Block			Insulator Block Size (see chart below)
					Length	Width	Height	
ADB1121	90°C	2-14AWG 	2-14AWG 	115	2.90	1.04	2.34	S
ADB112/01	90°C	2/0-14AWG 	2/0-14AWG 	175	2.90	1.04	2.34	S
ADB112501	90°C	250MCM-6AWG 	250MCM-6AWG 	310	4.00	1.71	2.62	M
ADB113501	90°C	350MCM-6AWG 	350MCM-6AWG 	350	4.00	1.71	2.62	M
ADB115001	90°C	500MCM-4AWG 	500MCM-4AWG 	380	4.00	1.71	2.62	M
ADB222/01	90°C	2/0-14AWG 	2/0-14AWG 	350	2.90	1.04	2.34	S
ADB223501	90°C	350MCM-6AWG 	350MCM-6AWG 	620	5.50	2.90	3.25	L
ADB225001	90°C	500MCM-4AWG 	500MCM-4AWG 	760	5.50	2.90	3.25	L

F


**COVERS (ONE COVER REQUIRED FOR EACH BLOCK ORDERED)**

CS*	S
CM	M
CL	L

\*FITS SIZE S MODULES EXCEPT ADB162/01, ADB222/01 & ADB2622/01



**INSULATOR BLOCK DIMENSIONS**



Insulator Block size	Dimensions									
	A	B	C	D	E	F	G	H	I	J
S	1.04	2.34	2.90	2.53	.18	.35	.20	.46	.19	.625 1.250
M	1.71	2.62	4.00	3.50	.25	.37	.20	.79	.20	1.250 1.875
L	2.90	3.25	5.50	5.00	.25	.50	.27	1.388	.29	2.250 3.250