

Project: _____ Type: _____

Drawn by: _____ Catalogue #: _____ Date: _____

Individual Spec Sheet

LED HIGH INTENSITY FILAMENT LAMP

ORDERING INFORMATION

Order code: 69598
Model number: ED23.5/20W/40K/BYP/EX39/V/FIL/ND/STD
UPC: 069549028111
Case quantity: 12

PHYSICAL DATA

Base: EX39
Shape: ED23.5

PERFORMANCE DATA

Watts (W): 20
Traditional equivalent (W) 75
Volts (VAC): 120-277
Color temperature (K)1: 4 000
Lumen output (lm)2: 3 500
Efficacy (lm/W): 175
CRI: 80
Life L70 (h)3: 25 000
Beam angle (°): Universal
Power factor: >0.9
Frequency (Hz): 50/60
Operating temp. range: Open Fixture: -30 °C to 50 °C (-22 °F to 122 °F)
 Enclosed Fixture: -30 °C to 45 °C (-22 °F to 113 °F)
 Indoor and Outdoor


Application (Indoor/Outdoor):

¹ Typical color temperature range: +/- 5 %.

² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.

³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations.

DIMENSIONS



3^{yrs}
warranty


**non
 dimmable**


**enclosed
 fixture**

66
**wet
 location**


Intertek

FC

This lighting equipment meets requirements of ICES-005 issue 5 class B for use in residential applications.
 Data is based upon tests performed in a controlled environment.
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.