

Individual Spec Sheet

L3CBA GEN. 2

LED RECESSED CENTER BASKET

3 CCT AND 3 POWER SELECTABLE

ORDERING INFORMATION

Order code: 69161
Model number: L3CBA-1LPS30P-Q/3C
UPC: 069549025011
Case quantity: 2
DLC unique ID: S-HCXGK6

PHYSICAL DATA

Dimensions: 1'X4'
Diffuser material: PMMA
Housing material: Steel
Mounting: Recessed inverted T-Bar ceilings

PERFORMANCE DATA

Watts (W): 20/25/30
Volts (VAC): 120-347
Color temperature (K)¹: 3 500/4 000/5 000
Lumen output (lm)²: 2 660/3 250/3 810
Efficiency (lm/W): 125
CRI: 80+
Life L70 (h)³: 189 000
Dimming: 0-10V
Power factor: 0.90
THD (%): 10
Operating temp. range: -25 °C to 55 °C (-13 °F to 131 °F)

¹ Typical colour temperature range: +/- 5 %
² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %
³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations

LUMEN SPECIFICATION TABLE

Order code	Model number	Watts (W)	3 500 K		4 000 K		5 000 K	
			Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)
69161	L3CBA-1LPS30P-Q/3C	20	2 640	132	2 660	133	2 680	134
		25	3 225	129	3 250	130	3 275	131
		30	3 780	126	3 810	127	3 840	128

DEFAULT PROGRAMMING
 30 W / 4 000 K

This lighting equipment complies with Canadian standard ICES-005 for use in commercial applications. Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.



COMPATIBLE ACCESSORIES

Part number	Type	Compatible with
CAS905-1X4	Surface mount kit 1'X4'	1'X4'
63490	Dry wall kit for 1'X4'	1'X4'

COMPATIBLE DIMMERS


Brand	Model number
Lutron	DVTV-WH, NTSTV-DV, NFTV
Leviton	DS710, IP710
Legrand	RH4FBL3PW

Dimming range 10%-100%.

Note: The above table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Stanpro recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation. Some dimmers may require more than one product for stable operation. The maximum number of products is determined by the dimmer wattage rating with LEDs. Be careful, these dimmers have different ratings depending on the product type. Again, refer to the dimmer installation instructions.

DIMENSIONS


1'X4'



PHOTOMETRIC DATA¹

69161 • L3CBA-1LPS30P-Q/3C • 30 W • 3 500 K • 3 883.2 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	1 049.5	27.0
0-40	1 712.4	44.1
0-60	3 027.6	78.0
60-90	844.6	21.7
70-100	356.5	9.2
90-120	3.8	0.1
0-90	3 872.2	99.7
90-180	11.1	0.3
0-90	3 883.2	100

Illuminance at a distance

Center beam fc		Beam width	
2.0'	339.4	5.0'	7.1'
4.0'	84.8	10.0'	14.1'
6.0'	37.7	15.0'	21.2'
8.0'	21.2	20.0'	28.2'
10.0'	13.6	25.1'	35.3'

■ Vert. spread: 102.8°
■ Horiz. spread: 120.9°

¹ Complete IES files available on our website.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.