

**APX410**

HIGH PERFORMANCE RECESSED DOWNLIGHT SERIES



NAME:	
TYPE:	
DATE:	
NOTES:	

**SPECIFICATIONS**


LIGHT UNIT:	Aluminum Die cast with powder paint coat preventing discoloring and rusting.
JUNCTION BOX:	Aluminum extrusion, with knockouts located at each end. Wiring compartment allows for (6) 14 gauge (AWG) insulated conductors. Connection to one (1) downstream unit is permitted within the junction box compartment. The compartment satisfies junction box volume requirements of CSA C22.2 No. 250.0/UL 1598.
INSTALLATION:	Ideal for ceiling installations with no housing required. Steel spring clip for easy installation. Suitable for installation in t-grid and drop ceiling applications. The APEX series is ideal for commercial applications, where a replacement for existing CFL/PL, fluorescent or incandescent fixtures are needed.
WIRING:	FT6 Plenum rated cable used to connect light unit and junction box.
OPTICS:	COB (Chip on Board) LED technology uses light guided reflector to distribute light and optimize high level of delivered lumens.
ELECTRICAL & PHASE CONTROL:	Easily connected to a 120V power supply via provided UL recognized driver. Standard 120-277V, 0-10V dimming driver. Optional 120V (3, 4, 6 & 8" only) or 347V (6 & 8" only) dimming driver available. Dimming down to 10% with most standard LED dimmers (see list of approved dimmers). Ambient operating temperature: -40°C (-40°F) to +40°C (+104°F). IC, DAMP Location and AIR-TIGHT rated. Phase Control: Forward Phase. Certifications: This product is ETL listed in USA & Canada, certified to UL standard 1598 and CSA standard C22.2 No. 250.0-08

CUTTING HOLE:	4.25" (108mm)
MOUNTING PLATE:	MP / AMP / MPHB 425
BEAM ANGLE:	80°
COLOR TEMPERATURE:	3K - 4K all finishes
CRI:	80+
LUMEN OUTPUT:	870 lumens
DIMMABLE:	Yes
WATTS:	12 watts
LED LIFE:	50,000 hours
WARRANTY:	5 years
WIRE CABLE:	FT6 rated
DRIVER (SPECIAL ORDER):	120V / 120-277V Option


**APPLICATIONS**

The Apex Regressed Series offers the latest high-performance LED (COB) recessed downlight with pressure-fit spring clips application for an easy install. Whether it is a Remodel or New Construction Installation, this unit is well suited for indoor / outdoor residential, hospitality, commercial and multifamily applications. It does not require a recessed housing for installation.

DIMENSIONS



ACCESSORIES



**MOUNTING PLATE**

Versatile square mounting plate allows for installation of all models of ndr lighting recessed lighting products. refer to our mounting plate compatibility chart to ensure the proper mounting plate is selected.



**ADJUSTABLE MOUNTING PLATE**

Versatile adjustable mounting plate allows for installation of all models of ndr lighting recessed lighting products. refer to our mounting plate compatibility chart to ensure the proper mounting plate is selected.



**MOUNTING PLATE WITH ADJUSTABLE HANGER BARS**

Versatile adjustable mounting plate allows for installation of all models of ndr lighting recessed lighting products. refer to our mounting plate compatibility chart to ensure the proper mounting plate is selected.



**VAPOUR BARRIER**

This vapour barrier unit may be used with all ndr lighting recessed lighting products. it is designed to prevent air leakage from your living space into the attic, or any insulated spaces.



**GOOF RINGS**

This goof ring is used when the ceiling hole is wider than the retrofit light unit being installed. refer to our goof ring compatibility chart to ensure the proper goof ring is selected.

RATINGS



ORDERING GUIDE

# APX410

HIGH PERFORMANCE RECESSED DOWNLIGHT SERIES

## APEX 410 SERIES

Series	Color Temperature	Finish
APX410-0510	3K 3000K/80CRI/12W	WH White
	4K 4000K/80CRI/12W	W/CH White/Chrome

**Notes:** Configure product using **BOLD** options: Ex: **APX410-0510-3K-W/CH**

## SPECIAL ORDER: APEX 410 SERIES

Series	Voltage Options	Color Temperature	Finish
APXS41	120V	3K 3000K/80CRI/12W	WH White
		4K 4000K/80CRI/12W	W/CH White/Chrome

**Notes:** Configure product using **BOLD** options: Ex: **APXS41-120V-3K-W/CH**