

Project: _____ Type: _____

Drawn by: _____ Catalogue #: _____ Date: _____

Individual Spec Sheet

WJM-L

LED JAM JAR

ORDERING INFORMATION

Order code: 69360
Model number: WJM-LS1A-W-3C-GY
UPC: 69549026780
Case quantity: 6

PHYSICAL DATA

Lens Material: Glass Frosted lens
Housing Material: Aluminum Die Cast
Mounting: 3 in 1 mounting type (ceiling, wall and threaded conduit)
¹ Not provided by factory

PERFORMANCE DATA

Watts (W): 21
Volts (V AC): 120 - 277
Color temperature (K): 3 000/4 000/5 000
Lumen output (lm): 2 679
Efficacy (lm/W): 128
CRI: 80
Life L70 (h): 50 000
Tested LM-80 (h): 9 000
Dimming: Yes
Power factor: >0.90
THD (%): ≤20
Frequency (Hz): 50/60
Surge protection (kV): 6
Input current (A): 0.2
Operating temp. range: -40°C to 40°C (-40°F to 104°F)

¹ Typical color temperature range: +/- 5 %.

² Lumen values are based on 4 000 K default programming. Please refer to the LUMEN SPECIFICATION TABLE for more details on other color temperatures.

³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations.

LUMEN SPECIFICATION TABLE

Order code	Model number	Watts (W)	3 000 K			4 000 K			5 000 K		
			Lumen output (lm)	Efficacy (lm/W)	LED Current (mA)	Lumen output (lm)	Efficacy (lm/W)	LED Current (mA)	Lumen output (lm)	Efficacy (lm/W)	LED Current (mA)
69360	WJM-LS1A-W-3C-GY	21	2 584	118	0.18	2 679	128	0.18	2 561	122	0.18

DEFAULT PROGRAMMING

69360: 4000 K



quick ship



LED fixture



dimnable fixture



wet location



IK08




ICES 005



This lighting equipment meets requirements of ICES-005 issue 5 class B for use in residential applications. Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

DIMENSIONS AND WEIGHTS




A in. (cm)	12.64 (32.09)
B in. (cm)	4 (10.14)
Net weight (lbs)	2.2

PHOTOMETRIC DATA¹

69360 • WJM-LS1A-W-3C-GY • 21W • 4000K • 2 679 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	281.3	10.5
0-40	494.3	18.5
0-60	1 162.8	43.4
60-90	956.6	35.7
70-100	742.5	27.7
90-120	387.8	14.5
0-90	2 119.4	79.1
90-180	559.5	20.9
0-180	2 678.9	100

Illuminance at a distance

Center beam fc		Beam width	
17'	1.27	269.7'	363.9'
34'	0.32	539.4'	727.9'
51'	0.14	809.1'	1 091.8'
68'	0.08	1 078.8'	1 455.7'
85'	0.05	1 348.5'	1 819.7'
102'	0.04	1 618.2'	2 183.6'

■ Vert. spread: 165.6°
■ Horiz. spread: 169.3°

¹ Complete IES files available on our website.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.