

# Notch

The Notch series of recessed downlights is characterized by a deep-set LED position which greatly reduces glare, neatly packaged in a price-conscious solution to general lighting.

**NEW** WET LOW-GLARE Intertek IC RATED

AIR TIGHT COLOR TEMPERATURE 2700k 3000k 3500k 4000k 5000k ENERGY STAR



Model	Size	Watts	Delivered lumens	CRI	Color °T	Voltage
<b>DRR4-CC</b>	4"	11 W	800 lm	90	2700, 3000, 3500,	120 V
<b>DRR6-CC</b>	6"	14 W	1000 lm		4000, 5000 K	

### Specifications

Every fixture includes a junction box with an integrated driver

Over 50,000 hours of service life

Can be daisy chained

Smooth 360° wide spread

100° beam angle

Minimal heat emission

Frosted lens

Edge lit technology

Switch-selectable CCT: 2700 K/3000 K/3500 K/4000 K/5000 K

Easy-access CCT switch on panel wire

IC certification (suitable for direct contact with insulation)

Air-tight certified as per ASTM E283-04

Suitable for wet locations

Ideal operating temperature: -20° to 40° C

Refer to website for dimmer compatibility

5-year warranty

### Finish

○ **WH** White

### Note

Other Color °T and Finishes available, but may require MOQ's and longer lead times. Please contact your DALs representative for more information.

### Order example

#### **DRR4-CC-WH**

White 4" deep recessed panel with 800 lumens at 3000 K

### Accessories

#### **RFP-46**

Rough-in plate

#### **RFP-UNI**

Universal rough-in plate

#### **DRR4-TRIM-BK**

4" recessed panel trim in black

#### **DRR4-TRIM-SBA**

4" recessed panel trim in sandblasted aluminum

#### **DRR6-TRIM-BK**

6" recessed panel trim in black

#### **DRR6-TRIM-SBA**

6" recessed panel trim in sandblasted aluminum



#### **DRR4-CC**

Ø4-1/4"



#### **DRR6-CC**

Ø6-1/2"

