



H8908B1002/U

24 Vac Duct or Wall Mounted Premier White® Humidistat

Overview

Mechanical humidity controllers provide automatic control of humidifiers and dehumidifiers or ventilators in central heating and air conditioning systems.

Features

- Fully enclosed, SPST, snap-acting, dust-proof switch are designed for wall or surface duct mounting
- H8909 and H46 models include Positive ON-OFF settings permit manual operation of controlled equipment.
- H600 models have a removable setting knob prevents tampering

Product Specifications

Dimensions (in.)	3 3/4 in. high x 3 1/4 in. wide x 2 in. deep
Dimensions (mm)	95.3 mm high x 82.6 mm wide x 50.8 mm deep
Temperature Range (F)	-20 F to +120 F
Temperature Range (C)	-29 C to +49 C
Mounting	Wall mount or Duct mount
Electrical Ratings	120 Vac, Full Load: 50 VA
Tradeline Value	Tradeline
Operating Humidity Range (% RH)	10 to 60% RH
Voltage	24 Vac
Type	Humidity Control
Color	Premier White®
Differential	4% to 6% RH