

PROFESSIONAL AV MOUNTING SOLUTIONS

QUICK REFERENCE GUIDE



FIXED DISPLAY WALL MOUNTS

Model	Product	Screen Size	Weight Capacity	Mounting Patterns (W,H)	Height Adjust	Model	Product	Screen Size	Weight Capacity	Mounting Patterns (W,H)	Height Adjust
XSM1U FUSION [®] SERIES		XL 55 - 100"	250 lbs. (113.4 kg)	100 x 100 - 1070 x 600 mm	1" (25 mm)	XSD1U		XL 55 - 100"	310 lbs. (140.6 kg)	50 x 50 - 200 x 200 mm	26" (660 mm)
LSM1U FUSION [®] SERIES		L 42 - 86"	200 lbs. (90.7 kg)	100 x 100 - 871 x 500 mm	1" (25 mm)	LSD1U FUSION [®] SERIES		L Varies by Screen Weight	122 - 175 lbs. (55 - 82 kg)	200 x 200 - 860 x 510 mm	15.75" (400 mm)
LSA1U FUSION [®] SERIES		L 42 - 86"	200 lbs. (90.7 kg)	100 x 100 - 870 x 500 mm	N/A	MSD1U FUSION [®] SERIES		M Varies by Screen Weight	67 - 125 lbs. (30 - 57 kg)	200 x 200 - 871 x 500 mm	15.75" (400 mm)
MSM1U FUSION [®] SERIES		M 32 - 65"	125 lbs. (56.7 kg)	100x 100 - 642 x 400 mm	1" (25 mm)	LSTU THININSTALL [™] SERIES		L 42 - 86"	125 lbs. (56.7 kg)	200 x 200 - 800 x 500 mm	N/A
MSA1U FUSION [®] SERIES		M 32 - 65"	125 lbs. (56.7 kg)	100 x 100 - 642 x 400 mm	N/A	MSTU THININSTALL [™] SERIES		M 32 - 65"	125 lbs. (56.7 kg)	100 x 100 - 600 x 400 mm	N/A
FSR1U		S 10 - 40"	45 lbs. (20.4 kg)	50 x 50 - 200 x 200 mm	N/A	OBIU		L 42 - 100"	310 lbs. (140.6 kg)	400 x 100 - 1020 x 500 mm	Lateral Shift: Min. 6.625" - 10.625" max (168 - 269 mm)

TILT DISPLAY WALL MOUNTS

Model	Product	Screen Size	Weight Capacity	Mounting Patterns (W,H)	Tilt	Model	Product	Screen Size	Weight Capacity	Mounting Patterns (W,H)	Tilt
XTM1U FUSION [®] SERIES		XL 55 - 100"	250 lbs. (113.4 kg)	100 x 100 - 1070 x 600 mm	+5°, -12°	MTMS1U FUSION [®] SERIES		M 32 - 65"	75 lbs. (34 kg)	200x 200 - 455 x 400 mm	+2°, -12°
LTM1U FUSION [®] SERIES		L 42 - 86"	200 lbs. (90.7 kg)	100 x 100 - 878 x 500 mm	+2°, -12°	STMS1U FUSION [®] SERIES		S 24 - 42"	75 lbs. (34 kg)	75 x 75 - 300 x 300 mm	+2°, -12°
LTA1U FUSION [®] SERIES		L 42 - 86"	200 lbs. (90.7 kg)	100 x 100 - 879 x 500 mm	+2°, -12°	LTTU THININSTALL [™] SERIES		L 32 - 65"	100 lbs. (45.4 kg)	200 x 200 - 800 x 500 mm	+ 0°, - 12°
MTM1U FUSION [®] SERIES		M 32 - 65"	125 lbs. (56.7 kg)	100 x 100 mm - 650 x 400 mm	+2°, -12°	MTTU THININSTALL [™] SERIES		M 26 - 47"	100 lbs. (45.4 kg)	100 x 100 - 600 x 400 mm	+ 0°, - 12°
MTMP1U FUSION [®] SERIES		M 43 - 47"	200 lbs. (90.7 kg)	100 x 100 - 571 x 600 mm	+5°, -12°	ODMLT OUTDOOR MOUNT SERIES		L 42 - 86"	175 lbs. (79.3 kg)	127 x 100 - 643 x 430 mm	+/-15°
MTA1U FUSION [®] SERIES		M 32 - 65"	125 lbs. (56.7 kg)	100 x 100 - 650 x 400 mm	+2°, -12°	FTR1U		S 10 - 40"	45 lbs. (20.4 kg)	50 x 50 - 200 x 200 mm	+5°, -15°

SWING ARM DISPLAY WALL MOUNTS

Model	Product	Screen Size	Weight Capacity	Mounting Patterns (W,H)	Extension	Model	Product	Screen Size	Weight Capacity	Mounting Patterns (W,H)	Extension
TS525TU* THININSTALL [™] SERIES		L 42 - 75"	125 lb. (56.7 kg)	100 x 100 - 800 x 400 mm	25" (635 mm)	TS18SU* THININSTALL [™] SERIES		S 10 - 40"	35 lbs. (15.9 kg)	75 x 75 - 200 x 200 mm	18" (457 mm)
TS325TU* THININSTALL [™] SERIES		M 32 - 65"	75 lbs. (34 kg)	100 x 100 - 600 x 400 mm	25" (635 mm)	TS110SU* THININSTALL [™] SERIES		S 10 - 40"	35 lb. (15.9 kg)	75 x 75 - 200 x 200 mm	9.9" (251 mm)
TS318TU* THININSTALL [™] SERIES		M 32 - 65"	75 lbs. (34 kg)	100 x 100 - 600 x 400 mm	18" (457 mm)	PDRUB		L 42 - 86"	200 lbs. (90.7 kg)	200 x 200 - 862 x 517 mm	37" (940 mm)
TS318SU* THININSTALL [™] SERIES		M 32 - 65"	75 lbs. (34 kg)	100 x 100 - 600 x 400 mm	18" (457 mm)	PNRUB		L 42 - 86"	200 lbs. (90.7 kg)	200 x 200 - 862 x 517 mm	25" (635 mm)
TS218SU* THININSTALL [™] SERIES		M 32 - 55"	75 lbs. (34 kg)	100 x 100 - 400 x 400 mm	18" (457 mm)	ODMLA25 OUTDOOR MOUNT SERIES		L 32 - 80"	150 lbs. (68 kg)	75 x 75 - 709 x 444 mm	21.6" (550 mm)

DESK MONITOR MOUNTS										
Model	Product	Monitor Configuration	Minimum Depth from Back of Desk	Maximum Extension	Manual Height Adjust	Dynamic Height Adjust	Weight Capacity (per monitor)	Colors		
KXD220		DUAL	2.45" (62 mm)	20.6" (400 mm)	N/A	13" (330 mm)	5 - 25 lbs (2.3 - 10 kg)	B S W		
KXC220		DUAL	2.45" (62 mm)	22.5" (571 mm)	7" (178 mm)	13" (330 mm)	5 - 25 lbs (2.3 - 10 kg)	B S W		
KXC330		TRIPLE	2.45" (62 mm)	22.5" (352 mm)	7" (178 mm)	13" (330 mm)	5 - 20 lbs (2.3 - 10 kg)	B S W		
KXC420		QUAD	2.45" (62 mm)	22.5" (523 mm)	7" (178 mm)	13" (330 mm)	5 - 20 lbs (2.3 - 10 kg)	B S W		
Model	Product	Dynamic Height Adjustment	Weight Capacity (per monitor)	Colors		Model	Product	Dynamic Height Adjustment	Weight Capacity (per monitor)	Colors
K1C110		13.0" (330 mm)	5 - 25 lbs. (2.3 - 11.3 kg)	B S W		K1D120		13.0" (330 mm)	5 - 25 lbs. (2.3 - 11.3 kg)	B S W
K1C120		13" (330.2 mm)	2.3 - 9.9 kg	B S W		K1D22H		13.0" (330 mm)	2 - 9 lbs. (0.9 - 4.1 kg)	B
K1C210		13" (330.2 mm)	5 - 25 lbs. (2.3 - 11.3 kg)	B S		K1D220		13.0" (330 mm)	5 - 25 lbs. (2.3 - 11.3 kg)	B S W
K1C22H		13" (330.2 mm)	5 - 25 lbs. (2.3 - 11.3 kg)	B S		K2C110		7.0" (178 mm)	40 lbs. (18.1 kg)	B S
K1C220		13" (330.2 mm)	5 - 25 lbs. (2.3 - 11.3 kg)	B S W		K2C120		7.0" (178 mm)	40 lbs. (18.1 kg)	B S
K1C330		13" (330.2 mm)	5 - 20 lbs. (2.3 - 9.07 kg)	B S W		K2C22H		7.0" (178 mm)	5 - 25 lbs. (2.3 - 11.3 kg)	B S
K1C420		13.0" (330 mm)	5 - 20 lbs. (2.3 - 9.07 kg)	B W		K2C220		7.0" (178 mm)	25 lbs. (11.3 kg)	B S

Various configurations and mounting options available on legrandav.com

IN-WALL STORAGE BOXES										
Model	Product	Weight Capacity	Dimensions	Colors		Model	Product	Weight Capacity	Dimensions	Colors
PAC525F		10 lbs. (4.5 kg)	9 x 14.25 x 3.9" (229 x 362 x 98 mm)	B W		PAC527F		40 lbs. (18.1 kg)	14.25 x 22 x 3.9" (362 x 559 x 98 mm)	B W
PAC526F		10 lbs. (4.5 kg)	14.25 x 14.25 x 3.9" (362 x 362 x 98 mm)	B W						

Various configurations and mounting options available on legrandav.com

COMPONENT STORAGE PANELS										
Model	Product	Weight Capacity	Dimensions	Features		Model	Product	Weight Capacity	Dimensions	Features
CSPH		20 lbs. (9 kg)	27.31 x 14.40 x 1.15" (693 x 366 x 29 mm)	Hinges 90° for ease of access to components		CSMP9X12		10 lbs. (4.5 kg)	12 x 9 x 0.5" (304 x 228 x 12 mm)	Mounts between any display and any universal mount
CSPR		20 lbs. (9 kg)	24.22 x 10.4 x 1.15" (615 x 264 x 29 mm)	Removable for component service without moving the display		CSSMP15X10		15 lbs. (6.8 kg)	22.71 x 10.61 x 0.5" (533 x 576 x 12 mm)	Slide out removable Lever Lock™ panel

Various configurations and mounting options available on legrandav.com

COMPONENT SHELVES								
Model	Product	Feature	Compatible		Model	Product	Feature	Compatible
FCA850		Fusion Side Camera Shelf	Side Shelf	Fusion series	PAC811		Video Conferencing Camera Shelf - 14", for XL Displays	Above/Below LPEIU/LFEIU
FCA800		Fusion 8" Above/Below Shelf for Large Displays	Above/Below	Fusion series	PAC870		Height-Adjustable Accessory Shelf	Below LPEIU/LFEIU
FCA810		Fusion 8" Above/Below Shelf for XL Displays	Above/Below	Fusion series	FCA611B		Fusion Small Height-Adjustable Accessory Shelf	Above/Below LPAU/LFAU
PAC810		Video Conferencing Camera Shelf - 9", for XL Displays	Above/Below	LPEIU/LFEIU	FCA612B		Fusion Large Height-Adjustable Accessory Shelf	Above/Below MPAU/MFAU/ LPAU/LFAU/XPAU