

Carolprene® with 17 FREE™ Jacketed Type SOOW

105°C, 600 Volt, UL/c(UL) Portable Cord



Features and Benefits

- No halogens
- More environmentally friendly
- Excellent resistance to oil and moisture
- Good tensile strength, elongation and aging characteristics
- High flexibility
- Excellent abrasion resistance
- Water-resistant*
- UL Listed for indoor and outdoor use
- Ozone-, sunlight (UV)- and weather-resistant
- TRU-Mark® sequential footage marking

Applications

- Portable tools and equipment
- Portable appliances
- Small motors and associated machinery

Industry Approvals

- UL/c(UL) Flexible Cord - UL 62/CSA 22.2 No. 49
- RoHS Compliant

* Suitable for immersion in water if properly sealed and terminated.



Data subject to change without notice.

COLOR CODE CHART

NO. OF CONDUCTORS	COLOR
2	Black, White
3	Black, White, Green
4	Black, White, Red, Green
5	Black, White, Red, Green, Orange



General Cable

4 Tessenere Drive
Highland Heights,
Kentucky 41076-9753

Telephone (800) 243-8020
Fax (859) 572-9262
info@generalcable.com
www.generalcable.com

Product Construction:

Conductors:

- 18 through 2 AWG fully annealed stranded bare copper

Insulation:

- Premium-grade, color-coded 105°C EPDM
- Color code: See chart below

Jacket:

- Carolprene®, Black, 17 FREE™
- Temperature range: -40°C to +105°C

Jacket Marking:

- CAROL (SIZE) (mm²) 105°C (UL) WATER RESISTANT SOOW WITH 17 FREE (-40°C) FT2 c(UL) 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)

Packaging:

- 250' (76.2 m), 500' (152.4 m), 1000' (304.8 m)
- Other put-ups available on special order



TYPE SOOW - 600 VOLT - UL/c(UL)

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOMINAL INS. THICKNESS		NOMINAL O.D.		CURRENT AMPS†	APPROX. NET WT. LBS/M ⁽⁶⁾	STD. CTN.
				INCHES	mm	INCHES	mm			
HF763*	2	18	16/30	0.030	0.76	0.345	8.76	10	65	250'
HF769*	3	18	16/30	0.030	0.76	0.365	9.27	10	80	250'
HF770*	4	18	16/30	0.030	0.76	0.390	9.91	7	94	250'
HF722*	2	16	26/30	0.030	0.76	0.370	9.40	13	77	250'
HF765*	3	16	26/30	0.030	0.76	0.390	9.91	13	94	250'
HF766*	4	16	26/30	0.030	0.76	0.420	10.67	10	114	250'
HF723*	2	14	41/30	0.045	1.14	0.510	12.95	18	154	250'
HF762*	3	14	41/30	0.045	1.14	0.535	13.59	18	171	250'
HF768*	4	14	41/30	0.045	1.14	0.575	14.61	15	209	250'
HF724*	2	12	65/30	0.045	1.14	0.570	14.48	25	168	250'
HF725*	3	12	65/30	0.045	1.14	0.595	15.11	25	223	250'
HF726*	4	12	65/30	0.045	1.14	0.650	16.51	20	276	250'
HF767*	2	10	104/30	0.045	1.14	0.620	15.75	30	230	250'
HF728*	3	10	104/30	0.045	1.14	0.660	16.76	30	289	250'
HF727*	4	10	104/30	0.045	1.14	0.715	18.16	25	351	250'
HF063*	3	8	133/29	0.060	1.52	0.840	21.33	40	450	250'
HF064*	4	8	133/29	0.060	1.52	0.945	24.00	35	580	250'
HF065*	5	8	133/29	0.060	1.52	1.030	26.16	28	700	250'
HF073*	3	6	133/27	0.060	1.52	0.980	24.89	55	637	250'
HF074*	4	6	133/27	0.060	1.52	1.080	27.43	45	830	250'
HF075*	5	6	133/27	0.060	1.52	1.200	30.48	36	1015	250'
HF083*	3	4	133/25	0.060	1.52	1.140	28.96	70	926	250'
HF084*	4	4	133/25	0.060	1.52	1.260	32.00	60	1145	250'
HF085*	5	4	133/25	0.060	1.52	1.365	34.67	48	1419	250'
HF093*	3	2	133/23	0.060	1.52	1.330	33.78	95	1367	250'
HF094*	4	2	133/23	0.060	1.52	1.460	37.08	80	1699	250'
HF095*	5	2	133/23	0.060	1.52	1.580	40.13	64	2066	250'

Cord furnished with UL and CSA labels.

* Non-stock item; minimum quantity purchase required.

† Green conductor for grounding only. Ampacities based on NEC Table 400.5(A)(1).

⁽⁶⁾Actual shipping weight may vary.



Going Green with General Cable

General Cable has accelerated its environmental commitment, addressing its green alternative approach by identifying greener opportunities and promoting green cabling solutions wherever feasible. This includes promoting our existing green products, partnering with key customers in their green endeavors, identifying and providing for green product gaps, and participating as a member of the United States Green Building Council (USGBC) and collaborative ventures such as the Green Suppliers Network (GSN).



General Cable Canada

156 Parkshore Drive
Brampton, Ontario L6T 5M1
Telephone (800) 561-0649
Fax (800) 565-2529
info@generalcable.com

GENERAL CABLE, 17 FREE, CAROL BRAND, CAROLPRENE and TRU-MARK are trademarks of General Cable Technologies Corporation.

©2012. General Cable Technologies Corporation. Highland Heights, KY 41076
All rights reserved.
Printed in USA

Form No. CAR-0143-1112
43025