






StrongHold™ Product Full Line Offering

StrongHold™ General Purpose Tape

ST 14	ST14		ST 17	ST17		ST 15	ST15	
		<p>Excellent conformability properties and ease of tearing due to high elongation. Non-corrosive and pressure-sensitive adhesive which eliminates the need for catalysts during application. Flame retardant as well as cold resistant. Suitable as a primary insulation when used for splicing up to 600V.</p>			<p>Excellent conformability properties and ease of tearing due to high elongation. Non-corrosive and pressure-sensitive adhesive which eliminates the need for catalysts during application. Flame retardant as well as cold resistant. Suitable as a primary insulation when used for splicing up to 600V.</p>			<p>Non-corrosive and pressure-sensitive adhesive which eliminates the need for heat, moisture or other catalysts to affect the application. High elongation, nonflammable and able to be used in various weather conditions. Suitable as a primary insulation when used for splicing up to 600V.</p>

General Purpose	StrongHold™ Part Numbers	Case Quantity	Min. Order Qty.	Color	Thickness	Dimension
	ST17-075-66BU	100	20	Blue	7 mil	0.75" x 0.007" x 66'
	ST17-075-66BR	100	20	Brown	7 mil	0.75" x 0.007" x 66'
	ST17-075-66GY	100	20	Gray	7 mil	0.75" x 0.007" x 66'
	ST17-075-66GR	100	20	Green	7 mil	0.75" x 0.007" x 66'
	ST17-075-66OR	100	20	Orange	7 mil	0.75" x 0.007" x 66'
	ST17-075-66RD	100	20	Red	7 mil	0.75" x 0.007" x 66'
	ST17-075-66YL	100	20	Yellow	7 mil	0.75" x 0.007" x 66'
	ST17-075-66VI	100	20	Violet	7 mil	0.75" x 0.007" x 66'
	ST17-075-66WH	100	20	White	7 mil	0.75" x 0.007" x 66'
	ST14-075-60BK	100	20	Black	7 mil	0.75" x 0.007" x 60'
	ST15-075-66GRYL	100	20	Yellow with Green Stripes	5 mil	0.75" x 0.005" x 66'

StrongHold™ Full Product Offering

Nylon Cable Ties	Stainless-Steel Cable Ties	Terminals	Grounding Pigtails	Supports and Fasteners
				

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT®

©2020 Panduit Corp.
ALL RIGHTS RESERVED.
SFCB17--SA-ENG replaces
SFCB15--SA-ENG
01/2020