

# IN&SURE® Model 32, 33, 34 Push-In Wire Connectors

#### Installation Instructions: To be sold only with installation instructions.

**AWarning** Contact with electricity can cause electrical fires, personal injury, or death. Shut off power to the circuit before using this product and consult local building codes to determine installation requirements.

- 1. Wiring must comply with all applicable electrical codes.
- 2. Turn OFF power before removing or installing connectors.
- 3. Cleanly strip wires 1/2" (13mm).
- 4. Grip wire firmly and push conductor into open port. Slightly twist stranded wire counter clockwise while inserting. Use only one conductor per port.
- 5. Verify conductor is fully inserted to the back of the connector.
- 6. Connector is reusable on solid wires of the same wire gauge or larger. If reusing connector, cut and re-strip conductors.
- 7. In order to remove a wire, pull and twist the wire back and forth.

## Wire Ranges

•	
Solid (Reusable):	12 to 20 AWG
Stranded:	12 to 16 AWG (≤ 19 Strands)
	18 AWG Stranded (7 Strands) (Non-Reusable)


#### DO NOT use with 16 AWG (26 Strands)


DO NOT RE-USE connector on stranded wire.


COPPER TO COPPER ONLY: Do Not Use on Aluminum wire. Temperature Rating: 105°C (221°F) maximum. 600 volts maximum building wire. 1000 volts in signs and lighting fixtures.


For use on insulation types TFN, TFFN, THHN, XHHW, T90 nylon or equivalent.











## IDEAL INDUSTRIES, INC.

Sycamore, IL 60178, U.S.A. 800-435-0705 Customer Assistance www.idealind.com ND 6779-2



