

PHILIPS Lighting

Centium T5HO

CENTIUM ELE BALLAST (2) F54T5/HO 347-480V

No matter what the conditions require, operating at a variety of line voltages between 120V to 480V, whether located in high ambient temperature environments (requiring a 90° C rating) or not, our family of Philips Advance Centium ballasts are ideal for a wide variety of applications.

Product data

General Information		
Lamp Type	F54T5/HO	
Number of Lamps	1/2 piece/unit	
Ballast Type	Electronic Fluorescent	
Base Model	HCN2S5490CWL	
Suitable For Outdoor Use	Yes	
Automatic Restart	Yes	
Operating and Electrical		
Input Voltage	347-480 V	
Input Frequency	50 to 60 Hz	
Total Harmonic Distortion USA	10 %	
Ignition Method	Programmed Start	
Crestfactor (Nom)	1.7	
Ignition Time (Nom)	1.5 s	
Ballast Factor (Nom)	1	
Power Factor (Nom)	0.98	
Input Current (Max)	0.35 A	
Input Current (Min)	0.25 A	
Input Power (Nom)	120-119 W	
Rated Lamp Power	54 W	


Wiring	
Color Input Terminals	Black/Orange and Black/White
Color Output Terminals	RED, YEL & BLU
Wire Striplength	0.375 mm
Lamp Connection	Series
Wire Length by Color	No wires
Wire Gauge (Nom)	18AWG mm
Wire Type	Solid
Remote Wiring Configuration Allowed	Yes
Tandem Wiring Configuration Allowed	Yes
Through Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote Wiring	20'
Max Ballast-Lamp Distance Tandem Wiring	Blue = 20'
Max Ballast-Lamp Distance Through Wiring	Blue = 20'
Connector Type	Poke-In
Temperature	
T-Case Maximum (Nom)	90 ℃
Mechanical and Housing	
Housing Material	Metal
Housing	L

Centium T5HO

16.7" x 1.18" x 1.0"			
FCC Non-Consumer			
CSA certificate UL certificate CEC Listing			
RoHS Compliant			
A			
No			
CENTIUM ELE BALLAST (2) F54T5/HO			
347-480V			

EAN/UPC - Product	781087030660
Order code	913710845202
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	913710845202
Net Weight (Piece)	0.441 kg

Dimensional drawing



Product	A1	A2	B1	C1
CENTIUM ELE BALLAST (2) F54T5/HO	16.70 in	16.34 in	1.18 in	1.00 in
347-480V				



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com 2019, March 22 - data subject to change