

EXCLUSIVE GENERAC COMPOSITE GENPAD™

GENERAC®

A0003322319



Choose The #1 Selling Home Standby Generator Brand

Generac's proprietary lightweight high-strength composite GENPAD™ revolutionizes HSB Generator installs. Weighing only 33lbs, the composite pad is 82% lighter and gains a 20% greater load capacity than the 3" concrete GENPAD™, creating a hassle-free pad installation and handling experience. It fits all Air-Cooled Generac 10-26kW automatic standby generators, plus Honeywell, and the limited warranty is active for the full length of the Generator warranty coverage. Available in both the US and Canada.

Features & Benefits:



STRONG AND LIGHTWEIGHT

Easy to maneuver by one person and an increased load capacity compared to the concrete GENPAD™.



EASY TO TRANSPORT

Nesting design for easy stacking and stability during transit. Also resistant to cracking, chipping or breakage reducing waste and returns.



DURABLE DESIGN

Industrial high strength, fiberglass reinforced, thermoset sheet molding compound that is UV resistant and flammability rated.



NATURAL LOOK

Textured top surface and concrete gray color.



INSTALLATION MADE EASY

Mounting bolt score marks for quick unit alignment, and less installation time compared to pea gravel, poured in place concrete and concrete pads.



Pad Comparison

Place Your Composite GENPAD™ Order Today

Accounts with access to GENservice, place all orders through the portal.

Accounts without access to GENservice, contact AfterSales@generac.com.

	Good	Better	Best	
PRODUCT NAME	PEA GRAVEL*	CONCRETE GENPAD™	COMPOSITE GENPAD™	OTHER MANUFACTURER COMPOSITE PADS
Model Number	N/A	10000007852	A0003322319	-
Generac Approved Method	Minimum recommended	Recommended	Recommended	Not Recommended
Length in (cm)	54" (137cm)	54" (137cm)	54" (137cm)	56" (142cm)
Width in (cm)	31" (79cm)	31" (79cm)	31" (79cm)	38" (97cm)
Height in (cm)	3" (8cm) - 5" (13cm) stamped	3" (8cm)	3" (8cm)	5" (13cm)
Dry Unit Weight lbs (kg)	200 lbs (91kg)	186 lbs (84kg)	33 lbs (15kg)	44 lbs (20kg)
Strength	N/A	1,000 lbs (454kg)	1,200 lbs (544kg)	-
Color	N/A	N/A	Dark Grey	Black
Textured	N/A	No	Yes	No
Material	Pea gravel	Formulated concrete reinforced with rebar and fibers	Fiberglass reinforced thermoset sheet molding compound	Low density polyethylene
Fitment	Generac and Honeywell	Generac and Honeywell	Generac and Honeywell	No fitment
Hardware Included	N/A	Yes – Zinc Plated	Yes – Zinc Plated	Yes – Stainless Steel
Mounting Holes	N/A	Zinc Inserts	High nut insert spinout	Brass inserts
UV Rated	N/A	N/A	Yes – UL746C	Yes
Fire Rated	NFPA 37	NFPA 37	UL 94-5V, NFPA 37	NFPA 37
Storage	Heavy, multiple bags	Heavy	Lightweight, compact and nestable	Lightweight, not interlocking
Easy one person handling/carrying	No	No	Yes	Yes
Warranty	None	Active for the full length of the Generator warranty coverage period		One year

*Specifications based on average use cases.