



HYTOOL™ Hand-Operated Crimper, Installs #14 - 4/0 AWG, Permanent O and D3 grooves

By Burndy
Catalog # MD68



Crimper, Installs #14-4/0 AWG, O & D3 Grooves.

Features

- Ergonomically designed, one-piece, composite polymer handles
- Comfort grip handles
- Time-proven steel jaw designs
- No tool adjustment required
- 99,000 crimp/cycle life
- Positive lock, spring loaded die retainer buttons
- PTFE impregnated steel/bronze bushings and stainless steel pins
- Electroless nickel plated jaws and jaw links

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors
Crimp Force Capacity	4.5 ton
Die Type	W Die and X Die
EU RoHS Indicator	Yes
Sub Brand	HYTOOL
Tool Type	Hand Operated Crimper
Trade Name	HYTOOL™
UPC	781810446553
UPC 12 Digit	7818104465533

Dimensions

Length	25.38 in
Weight	6 lb
Width	7.04 in

Conductor Related

Crimping Ranges	Copper: 10 sol. - 500 Kcmil; Copper Flex: #8 to 350 kcmil
-----------------	--

Certifications and Compliance

Standards - RoHS Compliance EX
Status

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SE068728](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-MD68-SPEC-EN | REV 5/2023