

Full Cycle Ratchet Crimper, Dieless, 6000 lbs, Installs Service Entrance Splice Connectors #10 AWG - #1/0 AWG

By Burndy Catalog # OH25

Full Cycle Ratchet Crimper, Dieless, Service Entrance.



Features

- Heat treated steel
- 1/4" hole for snap fastener
- Forged steel jaws
- Nest die
- · Comfort grip handles
- Spring loaded handles
- · Protected ratchet mechanism
- · Replacement stainless steel indentor

Application

Crimping

General

Application - For Use On Service Entrance Splices

Die Type Dieless
EU RoHS Indicator Yes
Sub Brand HYTOOL

Tool Type Full Cycle Ratchet Crimper,

Dieless

 Trade Name
 HYTOOL™

 UPC
 781810452004

 UPC 12 Digit
 78181045200444

Dimensions

Dimensions 12.00 in x 3.75 in x 1.30 in

 Height
 1.30 in

 Length
 12.00 in

 Weight
 2.687 lb

 Width
 3.75 in

Conductor Related

Crimping Ranges Aluminum: #10 AWG - #1/0

 ΔWC

Certifications and Compliance

Standards - RoHS Compliance EX

Status

Logistics

Minimum Pack Quantity 1

Package Contents Tool only

Product Assets

Customer Notices - Prop 65 Notice

Sales Drawings - 210780

