

Eaton 11102A6513

Catalog Number: 11102A6513

Eaton Comet 18mm tubular photoelectric sensor, Through Beam, Forward Viewing, Power, 6.6 ft, PVC, Used with 80 ft detectors, 20-264 Vac 50/60 Hz, 15-30 Vdc (NPN)

General specifications



Product Name	Catalog Number
Eaton Comet 18mm tubular photoelectric sensor	11102A6513
	UPC 782113887067
Product Length/Depth	Product Height
2.75 in	0.71 in
Product Width	Product Weight
0.47 in	0.5 lb
Warranty	Certifications
3 year	UL Recognized cUL Recognized

defaultTaxonomyAttributeLabel

Cable type

Polyvinyl Chloride (PVC)

Used with

Used with 80 ft detectors

Enclosure material

Polyurethane foam (RIM)

Series

Comet

Sensor type

Through beam

Input voltage

20-264 Vac at 50/60 Hz, 15-30 Vdc (NPN)

LED indicator

Power

Cord length

79.2 ft

Operating temperature - max

158 °F

Operating temperature - min

-4 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 4, NEMA 4X, NEMA 6, NEMA 12,
NEMA 13, IP69K

Resources

Brochures

Comet series - Photoelectric sensors

Catalogs

Eaton's Volume 8—Sensing Solutions

Product Range Catalog Sensors – products, basic information, applications

Specifications and datasheets

Eaton Specification Sheet - 11102A6513



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia