

# Eaton E50ST

Catalog Number: E50ST

Eaton E50 NEMA heavy duty plug-in limit switch, 10A at 240Vac, 1A at 125Vdc, 1NO-1NC, Die Cast Zinc, NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, 10A, 1A, 14° to 250°F (-10° to 121°C)



## General specifications

Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit switch	E50ST
	UPC
	782113308814
Product Length/Depth	Product Height
1.54 in	3.13 in
Product Width	Product Weight
1.78 in	0.3313 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
UL Listed	
CSA Certified	

Contact Rating

10A at 240Vac, 1A at 125Vdc

Enclosure material

Die cast zinc

Contact configuration

1 NO-1 NC

Operating temperature - max

250 °F

Operating temperature - min

14 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,  
NEMA 6P, NEMA 13, IP67

Maximum AC current

10 A

Maximum DC current

1 A

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50ST](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)