

# eldoLED®

## FieldSET™ Programmable LED Drivers for Field Replacement



## A Simple Solution for Replacing Failed LED Drivers in the Field

FieldSET™ LED Drivers from eldoLED allow replacement of almost any failed driver in the field with a solution that matches power, output current, and dimming level requirements.

Installation is quick and hassle-free. We provide a selection of nine replacement drivers that cover most commercial lighting installations, reducing SKU complexity and inventory costs for distributors.

The FieldSET handheld programming tool provides visual and audible feedback during programming. This battery-operated handheld tool does not require a computer to operate, making it versatile and simple to use. When installing FieldSET replacement drivers, electrical contractors can program the output current with 1mA of resolution and dim levels to 1%, 5% or 10%.

- Quick, hassle-free installation with programmable replacement drivers
- Nine driver SKUs for servicing linear, compact, and industrial fixture types
- Contractor-friendly, battery-operated programming tool
- Provides visual/audible feedback during programming
- No compromising the light output of your installed fixtures




# eldoLED

## Field Programming and Replacement Made Easy!



The battery-powered FieldSET Driver Programming Tool allows you to set the desired dimming and current levels of the FieldSET driver without the need to connect to a laptop computer.



The cable assembly connects to the FieldSET driver for programming. The cable also allows the programmer to read settings from existing OPTOTRONIC drivers being replaced in the field.



Once the desired settings are in the FieldSET Programmer Tool, settings are communicated to the replacement driver for installation!\*

## Field-Replaceable Driver Solutions for Existing Luminaires...



Indoor Linear



Indoor Compact



Industrial & Outdoor

## FieldSET Drivers and Programming Tool

| Programmer   | Description  | UPC                               |              |
|--|--|-----------------------------------|--------------|
| FieldSET Driver Programming Tool                     | FieldSET Driver Handheld Programming Tool w/ Cable Assembly; 9V Battery Included | 196183313317                      |              |
| Fixture Type   | Driver Models (see specification sheets for complete product details)            | Driver Description                | UPC          |
| 2x2 and 2x4 troffers, linears, strips, architectural | FIELDSET OTi 30W UNV 1A0 1DIM DIM-1 FS   | 30W 120-277V; 0-10V, 1% min dim   | 196183325174 |
|  | FIELDSET OTi 50W UNV 1A4 1DIM DIM-1 FS   | 50W 120-277V; 0-10V, 1% min dim   | 196183325198 |
|  | FIELDSET OTi 85W UNV 2A3 1DIM DIM-1 FS   | 85W 120-277V; 0-10V, 1% min dim   | 196183325280 |
| Downlights (Compact Form Factor)                     | FIELDSET OTi 25W UNV 1A2 1DIM DIM-1 FS   | 25W 120-277V; 0-10V, 1% min dim   | 196183325228 |
|  | FIELDSET OTi 25W UNV 1A2 1DIM DIM-1 J-HOUSING FS                                 | 25W 120-277V; 0-10V, 1% min dim   | 196183325235 |
|  | FIELDSET OTi 40W UNV 1A4 1DIM DIM-1 FS   | 40W 120-277V; 0-10V, 1% min dim   | 196183325358 |
|  | FIELDSET OTi 40W UNV 1A4 1DIM DIM-1 J-HOUSING FS                                 | 40W 120-277V; 0-10V, 1% min dim   | 196183325341 |
| Industrial, high-bay, outdoor, cobra-head fixtures   | FIELDSET OTi 100W UNV 1250C 2DIM P6 FS J20                                       | 100W 120-277V; 0-10V, 10% min dim | 196183325389 |
|  | FIELDSET OTi 180W UNV 1250C 2DIM P6 FS J10                                       | 180W 120-277V; 0-10V, 10% min dim | 196183325402 |

For more information on FieldSET Driver solutions, visit [www.acuitybrands.com/FieldSET](http://www.acuitybrands.com/FieldSET)

\*For complete programming instructions, refer to our FieldSET LED Driver Programmer User Guide.