



# TBM45S COMFORT CRIMP® COMPRESSION TOOL WITH SHURE STAKE® MECHANISM

For Installing Color-Keyed<sup>®</sup> Copper and Aluminum

Lugs, Splices, C-Taps and Pigtails 8-2 AWG Cu, 10-6 AWG AI

**IMPORTANT:** Read and understand all of the instructions and safety information in this manual before operating or servicing this tool.








### **CRIMP ASSIST® Foot**

For larger wire and terminal combinations that require more force to complete the crimp, it may be useful to press the tool against a flat work surface (i.e. worktable, floor, etc.) to gain more leverage. The patent pending Crimp Assist<sup>™</sup> foot helps stabilize the tool during this type of operation.

Figure 3

1.2



1.4

#### Maintenance

Place CRIMP ASSIST<sup>®</sup> foot

flat on surface for

increased leverage.

- 1. Remove dust, moisture, and other contaminants with a clean brush or a soft, lint-free cloth.
- 2. DO NOT use on objects that could damage the tool.
- 3. Make certain all pins, pivot points, and bearing surfaces are protected with a THIN coat of any good SAE No. 20 motor oil. DO NOT oil excessively.
- 4. Keep handles closed when not in use to prevent objects from becoming lodged in the crimping dies.
- 5. Store tool in a cool, dry area.

# **GAGING VERIFICATION**

**NOTE:** Calibration verification procedure should be performed whenever damage or suspected damage has occurred or as often as operation conditions warrant.

FLAT WORK SURFACE

# 2.1

2.0

## **Visual Inspection**

Tool must be free of cracks, sharp edges and any other obvious imperfections that may affect performance of the tool. Nest area must be free of burrs, dents or scratches.

TABLE 1			
	TBM45S GAGING Requirements		
	NEST	GAGING MIN. – MAX.	
	RED	.175 – .187	
	BLUE	.212 – .224	
	GREY	.265 – .277	
	BROWN	.324 – .336	
	GREEN	.406 – .418	

# 2.2 Gaging Procedure 1. Wipe die nest before gaging. 2. Rotate wheel to desired nest. 3. Close handles until SHURE STAKE® mechanism just trips. 4. Insert gage pin into nest. The correct gage pin size should enter nest area freely with a minimum amount of finger pressure. The gaging shall fall with in the limits specified in Table A. For parts, service, repair and calibration, contact the Thomas & Betts

Tool Service Center at 1-800-284-TOOL (8665).

WARRANTY: Thomas & Betts sells this product with the understanding that the user will perform all necessary tests to determine the suitability of this product for the user's intended application. Thomas & Betts warrants that this product will be free from defects in materials and workmanship for the period stated on the enclosed warranty card. Upon prompt notification of any warranted defect, Thomas & Betts will, at its option, repair or replace the defective product or refund the purchase price. Proof of purchase is required. Misuse or unauthorized modification of the product voids all warranties.

Limitations and Exclusions: THE ABOVE WARRANTY IS THE SOLE WARRANTY CONCERNING THIS PRODUCT, AND IS IN LIEU OF ALL OTHER WARRANTIES EXPRESS OR IMPLIED, INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE, WHICH ARE SPECIFICALLY DISCLAIMED. LIABILITY FOR BREACH OF THE ABOVE WARRANTY IS LIMITED TO COST OF REPAIR OR REPLACEMENT OF THE PRODUCT, AND UNDER NO CIRCUMSTANCES WILL THOMAS & BETTS BE LIABLE FOR ANY INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES.