

Project: _____ Type: _____

Drawn by: _____ Catalogue #: _____ Date: _____

Individual Spec Sheet

YLD

LED YARD LIGHT

3 CCT AND 3 POWER SELECTABLE
Including a Twistlock Photocell

ORDERING INFORMATION

Order code: 69175
Model number: YLD-PS120A-W-3C-PT
UPC: 069549025127
Case quantity: 4
DLC Unique ID: S-YOVADZ

PHYSICAL DATA

Lens Material: Polycarbonate Lens
Housing Material: Heavy-duty cast aluminum
Mounting: Direct Wall Mount

PERFORMANCE DATA

Watts (W): 72/96/120
Volts (V AC): 120 - 277
Color temperature (K):¹ 3 000/4 000/5 000
Lumen output (lm):² 10 698 - 15 680
Efficacy (lm/W): 124
CRI: 80
Life L70 (h):³ 50 000
Beam angle (°): 133
Dimming: No
Power factor: >0.9
THD (%): <20
Frequency (Hz): 50/60
Surge protection (kV): 4
Environment: Wet
Input current (A): 0.9481
Operating temp. range: -40 °C to 45 °C

¹ Typical color temperature range: +/- 5 %.

² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.


³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations.



¹ Based on a maximum usage of 12 hours per day.
Not all products are qualified on the DLC QPL.
To view our DLC qualified products, please
consult the DLC Qualified Products List at
www.designlights.org/search.

This lighting equipment meets requirements of ICES-005 issue 5 class B for use in residential applications.
Data is based upon tests performed in a controlled environment.
Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

DIMENSIONS AND WEIGHT



A in. (cm)	13.48 (34.25)
B in. (cm)	9.48 (24.10)
C in. (cm)	6.87 (17.47)
Net weight (lbs)	4.79


ACCESSORIES (order separately)

Order code	Type
69176	15" ARM MOUNT KIT
PH0009	Shorting cap

PHOTOMETRIC DATA¹

69175 • YLD-PS120A-W-3C-PT • 120W • 4 000K • 15 303.6lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Lamp	% Fixture
0-30	3 287.6	21.5	21.5
0-40	5 639.4	36.8	36.8
0-60	11 138.6	72.8	72.8
60-90	3 710.6	24.2	24.2
70-100	1 559.1	10.2	10.2
90-120	320.1	2.1	2.1
0-90	14 849.2	97	97
90-180	454.4	3	3
0-180	15 303.6	100	100

Illuminance at a distance

Center beam fc		Beam width	
17.0'	13.8	83.7'	84.4'
34.0'	3.45	167.5'	168.9'
51.0'	1.54	251.2'	253.3'
68.0'	0.86	334.9'	337.8'
85.0'	0.55	418.7'	422.2'
102.0'	0.38	502.4'	506.6'

■ Vert. spread: 135.8°
■ Horiz. spread: 136.1°

¹ Complete IES files available on our website.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.