

Project: _____

Type: _____

Drawn by: _____ Catalogue #: _____

Date: _____

Individual Spec Sheet

L2STR

LED STRIP

3 CCT and 3 Power Selectable

ORDERING INFORMATION

Order code: 69391
Model number: L2STR-48LP40-Q/3C
UPC: 069549026995
Case quantity: 6
DLC unique ID: S-HQVFW6 (DLC Premium) / S-68UP5A (DLC Standard)

PHYSICAL DATA

Length in. (cm): 47 3/8 (120.34)
Lens material: Frosted PMMA
Housing material: 24 gauge white powder painted steel
Mounting: Surface, suspended or row mounted (V-Hooks and junction box cover included)

PERFORMANCE DATA

Watts (W): 25/30/40
Volts (V AC): 120-347
Color temperature (K)¹: 3 500/4 000/5 000
Lumen output (lm)²: 3 875/4 500/5 680
Efficacy (lm/W): 132
CRI: 80+
Life L70 (h)³: 156 000
Tested LM-80 (h)³: 10 000
Dimming: 0-10 V with 12 V auxiliary output
Power factor: 0.90
THD (%): 10
Frequency (Hz): 50/60
Surge protection (kV): 2.5
Input current (A): 0.21-0.07/0.25-0.09/0.33-0.12
Operating temp. range: -20 °C to 50 °C (-4 °F to 122 °F)

¹ Typical color temperature range: +/- 5 %.
² Lumen values are based on 4 000 K default programming. Please refer to the LUMEN SPECIFICATION TABLE for more details on other color temperatures.
³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations.

LUMEN SPECIFICATION TABLE

Watts (W)	3 500 K		4 000 K		5 000 K	
	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)
25	3 625	151	3 875	155	3 675	147
30	4 200	140	4 500	150	4 260	142
40	5 280	132	5 680	142	5 360	134

DEFAULT PROGRAMMING

40 W / 4 000 K



Not all products are qualified on the DLC QPL. To view our DLC qualified products, please consult the DLC Qualified Products List at www.designlights.org/search.

ACCESSORIES (order separately)

Order code	Type
68676	Suspension kit - 2 chains (1 m)
69082	10' Aviation cable kit with canopy, power cord & dimming wires
69405	Continuous row mounting connector
69398	Transparent end caps (set of 2)
69413	Wire guard kit 48"
69396	Replacement lens 48"


COMPATIBLE DIMMERS¹

Brand	Model
Leviton	IllumaTech IP710-LFZ DS710
Lutron	Maestro MS-Z101 Nova T NTSTV DIVA DVSTV
Legrand	RH4FBL3PW
Philips	Sunrise SR1200ZTUNV

Dimming range: 0%-100%

¹ This table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Some dimmers may require more than one product for stable operation. Stanpro recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation.

DIMENSIONS AND WEIGHT




Net weight (lbs)	4.4
------------------	-----

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

PHOTOMETRIC DATA¹

69391 • L2STR-48LP40-Q/3C • 25 W • 4 000 K • 3 871.8 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	850.9	22%
0-40	1 393.4	36%
0-60	2 490.9	64.3%
60-90	1 001.9	25.9%
70-100	705.3	18.2%
90-120	303.9	7.8%
0-90	3 492.8	90.2%
90-180	379.0	9.8%
0-180	3 871.8	100%


Illuminance at a distance

Center beam fc		Beam width	
1.7'	380	4.2'	7.9'
3.3'	101	8.1'	15.3'
5.0'	44.0	12.2'	23.1'
6.7'	24.5	16.4'	31.0'
8.3'	16.0	20.3'	38.4'
10.0'	11.0	24.4'	46.3'

■ Vert. spread: 101.4°
■ Horiz. spread: 133.3°

69391 • L2STR-48LP40-Q/3C • 30 W • 4 000 K • 4 496.9 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	987.0	21.9%
0-40	1 616.3	35.9%
0-60	2 889.4	64.3%
60-90	1 163.5	25.9%
70-100	819.7	18.2%
90-120	354.5	7.9%
0-90	4 052.9	90.1%
90-180	443.9	9.9%
0-180	4 496.9	100%


Illuminance at a distance

Center beam fc		Beam width	
1.7'	441	4.2'	7.9'
3.3'	117	8.1'	15.3'
5.0'	51.0	12.3'	23.2'
6.7'	28.4	16.4'	31.1'
8.3'	18.5	20.4'	38.5'
10.0'	12.7	24.5'	46.4'

■ Vert. spread: 101.6°
■ Horiz. spread: 133.4°

69391 • L2STR-48LP40-Q/3C • 40 W • 4 000 K • 5 675.6 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	1 243.7	21.9%
0-40	2 036.9	35.9%
0-60	3 642.1	64.2%
60-90	1 469.0	25.9%
70-100	1 036.0	18.3%
90-120	448.9	7.9%
0-90	5 111.1	90.1%
90-180	564.5	9.9%
0-180	5 675.6	100%

Illuminance at a distance

Center beam fc		Beam width	
1.7'	556	4.2'	7.9'
3.3'	148	8.1'	15.3'
5.0'	64.3	12.3'	23.3'
6.7'	35.8	16.4'	31.2'
8.3'	23.3	20.3'	38.6'
10.0'	16.1	24.5'	46.5'

■ Vert. spread: 101.5°
■ Horiz. spread: 133.5°

¹ Complete IES files available on our website.

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.