

Project:		Type:
Drawn by:	Catalogue #:	Date:

# Individual Spec Sheet

# L2STR

# **LED STRIP**

3 CCT and 3 Power Selectable

# ORDERING INFORMATION

Order code: 69394

Model number: L2STR-96LP90-Q/3C 069549027022 UPC:

Case quantity:

**DLC** unique ID: S-5FR32B (DLC Premium) / S-52TLY8 (DLC Standard)

# **PHYSICAL DATA**

Length in. (cm): 94 1/4 (239.34) Lens material: Frosted PMMA

24 gauge white powder painted steel **Housing material:** 

Mounting: Surface, suspended or row mounted (V-Hooks and junction box cover included)

## PERFORMANCE DATA

Watts (W): 65/75/90 Volts (V AC): 120-347

Color temperature (K)1: 3 500/4 000/5 000 Lumen output (lm)2: 9 750/11 100/12 780

Efficacy (Im/W): 135 CRI: +08 Life L70 (h)3: 156 000 Tested LM-80 (h)3: 10 000

**Dimming:** 0-10 V with 12 V auxiliary output

Power factor: 0.90 THD (%): 10 Frequency (Hz): 50/60 Surge protection (kV): 2.5

Input current (A): 0.54-0.19/0.63-0.22 /0.75-0.26 Operating temp. range: -20 °C to 50 °C (-4 °F to 122 °F)

# **LUMEN SPECIFICATION TABLE**

Watts	3 500 K		4 00	00 K	5 00	00 K
(W)	Lumen output (Im)	Efficacy (Im/W)	Lumen output (Im)	Efficacy (lm/W)	Lumen output (Im)	Efficacy (Im/W)
65	9 100	140	9 750	150	9 230	142
75	10 350	138	11 100	148	10 500	140
90	12 150	135	12 780	142	12 060	134

#### **DEFAULT PROGRAMMING**

75 W / 4 000 K

This lighting equipment meets requirements of ICES-005 issue 5 class A for use in commercial applications Data is based upon tests performed in a controlled environment.

Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

















ship





damp location











Not all products are qualified on the DLC QPL. To view our DLC qualified products, please consult the DLC Qualified Products List at www.designlights.org/search.



<sup>&</sup>lt;sup>1</sup> Typical color temperature range: +/- 5 %.

<sup>2</sup> Lumen values are based on 4 000 K default programming. Please refer to the LUMEN SPECIFICATION TABLE for more details on other color temperatures.

<sup>3</sup> Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations.



# **ACCESSORIES** (order separately)

Order code	Туре		
68676	Suspension kit - 2 chains (1 m)		
69082	10' Aviation cable kit with canopy, power cord & dimming wires		
69405	Continuous row mounting connector		
69398	Transparent end caps (set of 2)		
69413	Wire guard kit 48"1		
69397	Replacement lens 96"		


<sup>&</sup>lt;sup>1</sup> For 96" luminaires, order 2 units

#### **COMPATIBLE DIMMERS<sup>1</sup>**

Brand	Model	
Leviton IllumaTech IP710-LFZ DS710		
Maestro MS-Z101  Lutron Nova T NTSTV  DIVA DVSTV		
Legrand	RH4FBL3PW	
Philips	Sunrise SR1200ZTUNV	


#### Dimming range: 0%-100%

#### **DIMENSIONS AND WEIGHT**



Net weight (lbs) 8.5

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.




<sup>&</sup>lt;sup>1</sup> This table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Some dimmers may require more than one product for stable operation. Stanpro recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation.



#### PHOTOMETRIC DATA<sup>1</sup>

# 69394 • L2STR-96LP90-Q/3C • 65 W • 4 000 K • 9 743.1 lm


#### Polar candela distribution



## Zonal lumen summary


Zone	Lumens	% Fixture
0-30	2 130.1	21.9%
0-40	3 487.7	35.8%
0-60	6 237.0	64%
60-90	2 526.7	25.9%
70-100	1 788.3	18.4%
90-120	780.9	8%
0-90	8 763.7	89.9%
90-180	979.4	10.1%
0-180	9 743.1	100%

#### Illuminance at a distance



# 69394 • L2STR-96LP90-Q/3C • 75 W • 4 000 K • 11 091.0 lm

#### Polar candela distribution



#### Zonal lumen summary


Zone	Lumens	% Fixture
0-30	2 424.3	21.9%
0-40	3 969.6	35.8%
0-60	7 099.2	64%
60-90	2 875.5	25.9%
70-100	2 034.9	18.3%
90-120	889.2	8%
0-90	9 974.7	89.9%
90-180	1 116.3	10.1%
0-180	11 091.0	100%

#### Illuminance at a distance

	Center beam fc		Beam	width
1.7'	1 084		4.2'	7.9'
3.3'	288		8.1'	15.3'
5.0'	125		12.3'	23.2'
6.7'	69.8		16.5'	31.2'
8.31	45.5		20.4'	38.6'
10.01	31.3		24.6'	46.5'
	Vert. spread: Horiz. spread:	101.8° 133.4°		

# 69394 • L2STR-96LP90-Q/3C • 90 W • 4 000 K • 12 770.5 lm


### Polar candela distribution



# **Zonal lumen summary**

Zone	Lumens	% Fixture
0-30	2 786.8	21.8%
0-40	4 563.1	35.7%
0-60	8 162.1	63.9%
60-90	3 310.5	25.9%
70-100	2 344.6	18.4%
90-120	1 028.6	8.1%
0-90	11 472.6	89.8%
90-180	1 297.9	10.2%
0-180	12 770.5	100%

### Illuminance at a distance



Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

<sup>&</sup>lt;sup>1</sup> Complete IES files available on our website.