## SIEMENS

## Data sheet

## 3SU1550-0AA10-0AA0






holder, universal, 3-way, plastic/metal, minimum order quantity 5 or a multiple thereof

product brand name	SIRIUS ACT		
product designation	Holders		
design of the product	holder, universal for plastic/metal		
product type designation	3SU1		
manufacturer's article number			
<ul> <li>of the supplied holder</li> </ul>	<u>3SU1550-0AA10-0AA0</u>		
Actuator			
design of the actuating element	3-way without module		
number of contact modules	0		
Holder			
material of the holder	Plastic		
Display			
number of LED modules	0		
General technical data			
product function positive opening	No		
product component			
• diode	No		
lamp transformer	No		
light source	No		
series resistor	No		
insulation voltage rated value	500 V		
degree of pollution	3		
surge voltage resistance rated value	6 kV		
shock resistance			
<ul> <li>according to IEC 60068-2-27</li> </ul>	sinusoidal half-wave 15g / 11 ms		
<ul> <li>for railway applications according to EN 61373</li> </ul>	Category 1, Class B		
vibration resistance			
<ul> <li>according to IEC 60068-2-6</li> </ul>	10 500 Hz: 5g		
<ul> <li>for railway applications according to EN 61373</li> </ul>	Category 1, Class B		
reference code according to IEC 81346-2	U		
Substance Prohibitance (Date)	10/01/2014		
Auxiliary circuit			
number of NC contacts for auxiliary contacts	0		
number of NO contacts for auxiliary contacts	0		
Connections/ Terminals			
tightening torque of the screws in the bracket	1 1.2 N·m		
tightening torque			

• for grounding	0.8 1 N·m			
mbient conditions				
ambient temperature				
during operation	-25 +70 °C			
during storage	-40 +80 °C			
environmental category during operation according to IEC 60721		3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 95%, no condensation in operation permitted)		
invironmental footprint	<u>·</u> ·	,		
Environmental Product Declaration(EPD)	Yes			
Global Warming Potential [CO2 eq] total	0.593 kg	0.593 kg		
Global Warming Potential [CO2 eq] during manufacturing	0.625 kg			
Global Warming Potential [CO2 eq] during operation	0.235 kg			
Global Warming Potential [CO2 eq] after end of life	-0.267 kg			
Siemens Eco Profile (SEP)	Siemens EcoTech			
nstallation/ mounting/ dimensions				
<ul> <li>fastening method</li> </ul>	without			
<ul> <li>fastening method of modules and accessories</li> </ul>	Front plate mounting			
height	40 mm			
width	30 mm			
shape of the installation opening	round			
installation width	30 mm			
installation depth	30.1 mm			
thickness of the front plate usable pprovals Certificates	1 6 mm			
Test Certificates Marine / Shipping	Lloyds us Prs	UL	<b>D I I I L</b> other <u>Confirmation</u>	
Environment				
	nmental Con- rmations			
urther information				
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/10981 Information- and Downloadcenter (Catalogs, Brochure https://www.siemens.com/ic10 Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/prod Cax online generator http://support.automation.siemens.com/WW/CAXorder/def Service&Support (Manuals, Certificates, Characteristic https://support.industry.siemens.com/cs/ww/en/ps/3SU156	s,) uct?mlfb=3SU1550-0AA10-0AA0 ault.aspx?lang=en&mlfb=3SU1550-0A/ :s, FAQs,)	<u>\10-0AA0</u>		
Image database (product images, 2D dimension drawin http://www.automation.siemens.com/bilddb/cax_de.aspx?r	ngs, 3D models, device circuit diagra	ms, EPLAN macros,)		



last modified:

2/7/2024 🖸