

Project: _____ Type: _____
 Drawn by: _____ Catalogue #: _____ Date: _____

Individual Spec Sheet

WSL CHOICE
LED SLIM WALL PACK
 3 CCT AND 3 POWER SELECTABLE
 INTEGRATED PHOTOCELL

ORDERING INFORMATION

Order code: 69724
Model number: WSL-PS80-Q-3C-BR/CHOICE
UPC: 069549029453
Case quantity: 1
DLC unique ID: in process

PHYSICAL DATA

Finish: Bronze
Housing material: Die-cast aluminum
Lens material: Prismatic tempered glass

PERFORMANCE DATA

Watts (W): 40/60/80
Volts (V AC): 120-347
Color temperature (K)¹: 3 000/4 000/5 000
Lumen output (lm)²: 5 600/8 400/11 200
Efficacy (lm/W): 140
CRI: 80+
Life L70 (h)³: 50 000
THD (%): 20
IP rating: IP65
IK rating: IK08
Dimming: 0-10 V
B.U.G. rating: B1 U3 G4
Power factor: 0.91
Photocell: Yes
Surge protection (kV): 6
Operating temp. range: -40°C to 40°C (-40°F to 104°F)

¹ Typical colour temperature range: +/- 5 %.
² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.
³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations.

LUMEN SPECIFICATION TABLE

| Watts (W) | 3 000 K | | 4 000 K | | 5 000 K | |
|-----------|-------------------|-----------------|-------------------|-----------------|-------------------|-----------------|
| | Lumen output (lm) | Efficacy (lm/W) | Lumen output (lm) | Efficacy (lm/W) | Lumen output (lm) | Efficacy (lm/W) |
| 40 | 5 480 | 136 | 5 649 | 142 | 5 830 | 144 |
| 60 | 7 979 | 134 | 8 321 | 142 | 8 459 | 141 |
| 80 | 10 451 | 131 | 10 930 | 138 | 10 982 | 137 |

DEFAULT PROGRAMMING
 80 W / 4 000 K

This lighting equipment meets requirements of ICES-005 issue 5 class B for use in residential applications. Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.




Bronze

3 CCT/Power Selectable
 3 000/4 000/5 000 K
 5 yrs warranty
 quick ship
 LED fixture
 dimmable fixture
 wet location
 IK08
 ICES 005
 DLC LISTED PREMIUM
 UL CERTIFIED
 RoHS

ACCESSORY (order separately)

| Order code | Type |
|------------|-----------|
| 69725 | Wireguard |




COMPATIBLE DIMMERS¹

| Brand | Model |
|---------|-------------------------|
| Lutron | NTSTV-DV, NFTV, DDTV-WH |
| Leviton | DS710, IP710 |
| Legrand | H4FBL3PW |

Dimming range: 0%-100%

¹ This table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Some dimmers may require more than one product for stable operation. Stanpro recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation.

DIMENSIONS AND WEIGHTS




| | |
|------------------|--------------|
| A in. (mm) | 13.82" (351) |
| B in. (mm) | 8.88" (2263) |
| C in. (mm) | 4.48" (114) |
| Net weight (lbs) | 9.1 |

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

PHOTOMETRIC DATA¹

69724 • WSL-PS80-Q-3C-BR/CHOICE • 80 W • 4 000 K • 10 920 lm

Polar candela distribution



Zonal lumen summary

| Zone | Lumens | % Fixture |
|--------|----------|-----------|
| 0-30 | 1 834.0 | 16.8 |
| 0-40 | 3 278.2 | 30 |
| 0-60 | 6 779.8 | 62.1 |
| 60-90 | 3 376.2 | 30.9 |
| 70-100 | 2 127.7 | 19.5 |
| 90-120 | 555.9 | 5.1 |
| 0-90 | 10 156.0 | 93 |
| 90-180 | 763.7 | 7 |
| 0-180 | 10 919.8 | 100 |

Illuminance at a distance

| Center beam fc | Beam width |
|----------------|-------------|
| 1.7' | 2.2' 3.5' |
| 3.3' | 4.3' 6.8' |
| 5.0' | 6.6' 10.3' |
| 6.7' | 8.8' 13.8' |
| 8.3' | 10.9' 17.0' |
| 10.0' | 13.1' 20.5' |

■ Vert. spread: 66.5°
■ Horiz. spread: 91.5°

¹ Complete IES files available on our website.

| Qty | Description | Price |
|-----|-------------|-------|
| | | |

I accept the specifications of the luminaire configuration mentioned above.

Name: _____

Company: _____

Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.