
# PHILIPS ADVANCE

# LED Driver

# Xitanium

180W 0.1-1.25A 0-10V Dimming with SimpleSet XI180C125V200BSF1




Philips Advance Xitanium outdoor LED drivers with SimpleSet technology are designed to give OEMs ultimate flexibility. With wide operating windows and simple programming, the drivers make it easy for luminaire manufacturers to design luminaires of different sizes and lumen levels for outdoor applications.

### Specifications


Input Voltage (Vac)	Output Power (W)	Output Voltage (V)	Output Current (A)	Efficiency@ Max Load and 75°C Case	Max Case Temp. (°C)	Input Current (A)	Max. Input Power (W)	THD @ Max Load (%)	Power Factor @ Max Load	Surge Protection (Combi- Wave, KV)	Envir. Protection Rating
120	180	70-200	0.1 - 1.25	91.5	Life - 85°C	1.87	10.0	<10%	- >0.95 6	6	UL damp & dry
277				94	UL - 90°C	0.72	198   <1	<15%		and Type HL	

### Enclosure

	In. (mm)
Case Length	8.31 (211)
Case Width	2.31 (58.6)
Case Height	1.48 (37.6)
Mounting Length	8.91 (226.3)
Overall Length	9.47 (240.5)



### Wiring Diagram



Dimming	Dimming Range (with specified dimmers)	Minimum Output Current (A)	
0-10V Analog Class 1 and 2 Wiring	10% ~ 100%	0.07	

#### **Features**

- 50,000+ hour lifetime<sup>1</sup>
- Programmable output current through SimpleSet
- Large operating window
- 6kV combi-wave surge rating to comply with ANSI C82.77-5 CAT C low

#### Benefits

- Enables long life luminaire designs
- $\cdot$  Fast and simple way of programming
- Enables fixture designs with wide variety of loads and adjustable current options
- No external surge protection required to pass C82.77-5 CAT C low

#### Application

- Area
- Roadway
- Parking garages
- Floodlights

#### **Electrical Specifications**

All the specifications are typical and at 25°C Tcase unless specified otherwise.

### **Product Data**

Order Information				
Full Product Code	XI180C125V200BSF1M (Mid-Pack, 10pcs/Box)			
Line Frequency	50/60Hz			
Min. Mains Voltage Operational	108 Vac			
Max. Mains Voltage Operational	305 Vac			
Output Information				
Maximum Open Circuit Voltage	270Vdc			
Output Current Ripple	15% max @ max lout			
(ripple = peak to average / average)	(Low frequency ripple ( ≤120Hz) content <5%)			
Output Current Tolerance	<5%			
(in performance window)				
Protections	Short Circuit, Open Circuit Protection for LED + and LED – and Temperature Foldback			
Features				
0-10V Dimming	150µA (±3%) source current from driver. See dim curve for detail.			
AOC (Adjustable Output Current)	0.1A-1.25A via SimpleSet (Factory Default at 1.05A)			
Additional SimpleSet	Adjustable Min Dim level,			
Configurable Features	Adjustable Lumen Output,			
	Adjustable Lumen Output Min,			
	OEM Write Protection			
<b>Environment &amp; Approbation</b>				
Operating Ambient Temp. Range	-40°C to +55°C			
Max Case Temperature (Tcase)	85°C for Life & 90°C for UL Safety			
Agency Approbations	UL 8750, CSA 250.13, UL Listed, ETL Class P			
Electromagnetic Compliance	FCC Title 47 Part 15 Class A			
Audible Noise	<24dB Class A			
Weight	2.1 Lbs / 0.95 kgs			

1. Philips Advance Xitanium LED drivers are manufactured to engineering standards correlating to a designed and average life expectancy of 50,000 hours of operation at maximum rated case temperature. Minimum 90% survivals based on MTTF modeling.

#### **Electrical Specifications**


All the specifications are typical and at 25°C Tcase unless specified otherwise.

### **0-10V Dimming Curve**

Dimming source current from the driver: 150µA (@ 0<Vdim<8V) Minimum dim level: 10% of lout setting as default Maximum output voltage on the dimming wires: 12V

### **Approved Dimmer List**


Manufacturer	Manufacturer Part Number	
Lutron	Visit www.lutron.com/ advance for a list of dimmers (Mark VII) that will work with this driver	
Leviton	IllumaTech IP7 series	
Philips	Sunrise - SR1200ZTUNV	



### **Electrical Specifications**

All the specifications are typical and at 25°C Tcase unless specified otherwise.

### **Driver Output Window**




### Notes

- 1. Factory default output current is 1.05A.
- 2. To get a 100% to 10% dimming range, the output current setting through AOC should be  $\geq$  700mA.
- 3. Factory default minimum dimming level is 10%. This can be adjusted between 10% and 100% using Philips MultiOne.

### **Electrical Specifications**

All the specifications are typical and at 25°C Tcase unless specified otherwise.


### **Output Current Vs. Driver Case Temperature**



### Note

There is ±5°C tolerance on the driver case temperature.


### Driver Lifetime vs. Driver Case Temperature



#### **Performance Characteristics**

Based on measurements on a typical sample at  $70^{\circ}$ C case. The accuracy of the measurements is within the tolerance of the measurement instruments.

### Efficiency Vs. Output Voltage at 120Vac






### Efficiency Vs. Output Voltage at 277Vac


#### **Performance Characteristics**

Based on measurements on a typical sample at  $70^{\circ}$ C case. The accuracy of the measurements is within the tolerance of the measurement instruments.


### Power Factor Vs. Output Power



## Total Harmonic Distortion (THD) Vs. Output Power



### **Inrush Current Info**



Vin	Ipeak	T (@ 10% of Ipeak)	
120 Vrms	53A	270µS	
277 Vrms	138A	256µS	

Inrush current is measured at peak of the corresponding line voltage. Source impedance per NEMA 410.

### **Lightning Surge Info**

ANSI Surge Type	Differential Mode (L-N)	Common Mode (L-G, N-G, L&N-G)
1.2/50 $\mu$ s Combination Wave (w/t 2 $\Omega$ )	6kV	6kV

### Isolation

Isolation	Input	Output	0-10V	Enclosure
Input	NA	2xU+1kV	2.5kV	2xU+1kV
Output	2xU+1kV	NA	2.5kV	2xU+1kV
0-10V	2.5kV	2.5kV	NA	2.5kV
Enclosure	2xU+1kV	2xU+1kV	2.5kV	NA

U = Max input voltage

### **UL Conditions of Acceptability**

Please contact your Philips representative for a copy of the latest UL Conditions of Acceptability (COA).

© 2016 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication. philips.com/leddrivers

