

# Eaton DG1-34105FB-C21C

Catalog Number: DG1-34105FB-C21C

Eaton PowerXL DG1 variable frequency drive, IP21 3ph-Input - 3ph-Output PowerXL Drive, 208-240V input 55 kW 75 Hp CT 3-phase 50/60 Hz 105A output IP21/type 1 enclosure FR6 LCD display



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton PowerXL DG1 variable frequency drive	DG1-34105FB-C21C
	<b>UPC</b>
	786685900643
<b>Product Length/Depth</b>	<b>Product Height</b>
43.5 in	15 in
<b>Product Width</b>	<b>Product Weight</b>
17.5 in	160 lb
<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000 generally applies with some exceptions. Drive products come with a standard 24 months from date of shipment and 36 months with Eaton certified start up all inclusive coverage parts labor and travel.	GoST-R C-Tick Compliant CE Marked RoHS Compliant
	<b>Certifications</b>
	cUL Listed UL Listed UL 508C EN ISO 13849-1 EN 62061 IEC 61508

## defaultTaxonomyAttributeLabel

### Brake chopper

Brake chopper

### Horsepower

75 hp

### Phase

Three-phase in, three-phase out

### Frequency rating

50-60 Hz

### Frame size

6

### Keypad

Included

### Input voltage

230 V, 208-240 V(-15%, +10%)

### Display

LCD graphical

### Torque rating

CT

### Communication

EtherNet, RS-485, BACnet MS/TP, Modbus TCP and RTU communication

### Enclosure

IP21/type 1

### Protection

Internal EMC filter, DC choke

### Output current - max

105 A

### Software

Active energy control, quick start wizard

### Number of slots

2 expansion slots

### Material

Coated board

### Power consumption

55 kW

## Resources

### Application notes

Load balancing in multi motor applications

PID controller

Smoke Mode and fire mode

Torque control

Connecting drives to generator supplies

Motor data and V/f curves

DG1 in pump and fan applications

Electromagnetic compatibility (EMC)

Analog I/Os

Real time clock and use of the timers

Operating at low temperatures

Digital I/Os

Starting, stopping and operation

Dual Rating What exactly does that mean?

### Catalogs

Eaton's Volume 6—Solid-State Motor Control

Product Datasheet - DG1-34105FB-C21C

Product Range Catalog Drives Engineering

### Installation instructions

PowerXL DG1 Series VFD Application Manual

PowerXL DG1 Series VFD Installation Manual

### Multimedia

PowerXL DG1 Variable Frequency Drive - Setup via WebUI

Power XL General Purpose Drives

### Specifications and datasheets

Eaton Specification Sheet - DG1-34105FB-C21C

#### Electromagnetic compatibility filter

EMC Filter

#### Internal DC choke

Yes

#### Conformal coated boards

Yes

#### User interface

Graphical Keypad

#### High overload (CT) amps

105 A

#### High overload (CT) kW

55 kW

#### High overload (CT) hp

75 hp

#### Low overload (VT) amps

140 A

#### Low overload (VT) kW

75 kW

#### Low overload (VT) hp

100 hp

#### Input voltage range

380 - 500 V

#### Input frequency range

50 - 60 Hz

#### Output frequency range

0 - 400 Hz

#### Max overload

110% for 1 minute

#### Recommended fuse size

175

#### Communications onboard

EtherNet/IP, Modbus TCP, RS-485: Modbus RTU, BACnet  
MS/TP

#### Motor control modes

Frequency, Speed, Open-loop speed, Open-loop torque

#### Motor type

Inductio, PM (IPM & SPM)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)