

RUH | OXFORD™

COMMERCIAL AND RESIDENTIAL UNIT HEATER



OXFORD™
SERIES | SÉRIE



A VERSATILE WORKHORSE

The RUH unit heater is small on price and big on heat. These heavy-duty units are well suited to situations where large amounts of heat must be provided in wide open spaces such as garages, workshops, commercial warehouses and construction sites. This unit has a powerful output up to 5000 W with a voltage of 240/208. The RUH has adjustable louvers that allow you to direct heat right from the source. With or without a built-in thermostat, it provides instant heat. Quiet, lightweight and easy-to-install with a universal wall or ceiling mounting bracket, this unit heater is everything you expect for less. Guaranteed productivity!

- **INSTANT HEAT**
- **ADJUSTABLE LOUVERS ALLOW YOU TO DIRECT HEAT**
- **WALL OR CEILING INSTALLATION SUPPORT BRACKET INCLUDED**
- **ENCLOSED AND PERMANENTLY LUBRICATED MOTOR**
- **2 KW TO 5 KW MODELS AVAILABLE**

COLOUR

- charcoal

FINISH

- epoxy-polyester powdercoat

MANUFACTURING

- 20-gauge steel cabinet
- totally enclosed and factory lubricated motor
- 350 CFM quiet helicoidal fan
- adjustable louvers
- thermal protection with automatic reset

ELEMENT

- nichrome element produces instant heat

CONTROL

- built-in thermostat (included with T series)
- wall thermostat (not included)

INSTALLATION

- wall or ceiling mounted with universal mounting bracket (included with unit)

WARRANTY

- three years

IDEAL FOR:

construction site, garage, workshop, small commercial space

°STELPRO

Stelpro reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. No returns accepted on optional-colour products. For all the latest models and prices, please refer to our website at www.stelpro.com.





TECHNICAL SPECIFICATIONS

WITHOUT CONTROL		BUILT-IN THERMOSTAT		24 V CONTROL		POWER	VOLTAGE	FLOW	THROW DISTANCE		HEAT RISE		WEIGHT	
CODE	PRICE	CODE	PRICE	CODE	PRICE	WATT S	VOLTS	CFM	M	FT	°C	°F	KG	LB
RUH2CHAR	519.00	RUH2TCHAR	538.00	RUH2C24CHAR	584.00	2000/1500	240/208	350	3	10	10	18	9	20
RUH3CHAR	528.00	RUH3TCHAR	546.00	RUH3C24CHAR	591.00	3000/2250	240/208	350	3	10	15	27	9	20
RUH4CHAR	538.00	RUH4TCHAR	556.00	RUH4C24CHAR	600.00	4000/3000	240/208	350	3	10	20	36	9	20
RUH5CHAR	545.00	RUH5TCHAR	562.00	RUH5C24CHAR	607.00	5000/3750	240/208	350	3	10	25	45	9	20

TECHNICAL DRAWINGS

