



Wire connector TA2.3 2 x 4 AWG...300 kcmil for 2 cables with control wire voltage tap-off 3 units accessories for: 3VA6 150/250

Model	
product brand name	SETRON
product designation	accessories
design of the product	circular conductor terminal
accessories	Wire connector
General technical data	
designation / of the terminal	TA2.3
type of electrical connection / with control wire tap	Yes
Connections according IEC	
connectable conductor cross-section	
<ul style="list-style-type: none"> for copper cable / stranded / minimum 	25 mm ²
<ul style="list-style-type: none"> for copper cable / stranded / maximum 	150 mm ²
<ul style="list-style-type: none"> for aluminum cable / stranded / minimum 	25 mm ²
<ul style="list-style-type: none"> for aluminum cable / stranded / maximum 	150 mm ²
stripped length	26 / 51 mm
tightening torque / when using copper cables	
<ul style="list-style-type: none"> stranded 	25 - 150 mm ² : 31.1 Nm
<ul style="list-style-type: none"> finely stranded 	25 - 150 mm ² : 31.1 Nm
Connections according UL	
permissible temperature / of connectable conductor / according to UL 486A-486B	75 °C
stripped length	1.0 / 2.0 in
connectable conductor cross-section	
<ul style="list-style-type: none"> for copper cable / stranded / minimum 	4 AWG
<ul style="list-style-type: none"> for copper cable / stranded / maximum 	300 kcmil
<ul style="list-style-type: none"> for copper cable / finely stranded / minimum 	4 AWG
<ul style="list-style-type: none"> for copper cable / finely stranded / maximum 	300 kcmil
<ul style="list-style-type: none"> for aluminum cable / stranded / minimum 	4 AWG
<ul style="list-style-type: none"> for aluminum cable / stranded / maximum 	300 kcmil
tightening torque / when using copper cables	
<ul style="list-style-type: none"> stranded 	4 AWG - 300 kcmil: 275 lb-in
<ul style="list-style-type: none"> finely stranded 	4 AWG - 300 kcmil: 275 lb-in
Further information	

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9243-0JC22>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9243-0JC22>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9243-0JC22

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

8/19/2022 

