



Contractor-grade MainsFit (UL Type-B) T8

14.5T8/CNG/48-835/MF17/G 25/1

The Contractor-grade MainsFit (UL Type B) lamps are designed to provide simple retrofit solution to move from traditional fluorescent lamps to energy saving LEDs. This ballast bypass lamp is similar to other UL Type B lamps in the Philips family by providing proven energy savings, long life (50k hours), surge suppression and industry leading safety features. All lamps in the Contractor-grade family are also double-ended to help simplify the installation.

Product data

| General Information | | LLMF At End Of Nominal Lifetime (Nom) 70 % | |
|------------------------------------|---------------------------------|--|-------------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] | | |
| Nominal lifetime | 50,000 hour(s) | | |
| Switching Cycle | 50,000 | | |
| Lighting Technology | LED | | |
| EU RoHS compliant | Yes | | |
| Light Technical | | Operating and Electrical | |
| Color Code | 835 [CCT of 3500K] | Line Frequency | 50 to 60 Hz |
| Beam Angle (Nom) | 240 degree(s) | Input Frequency | 50 to 60 Hz |
| Luminous Flux | 1,750 lm | Power Consumption | 14.5 W |
| Color Designation | White (WH) | Lamp Current (Max) | 125 mA |
| Correlated Color Temperature (Nom) | 3500 K | Lamp Current (Min) | 58 mA |
| Luminous Efficacy (rated) (Nom) | 120.00 lm/W | Wattage Equivalent | 32 W |
| Color Consistency | <6 | Starting Time (Nom) | 0.5 s |
| Color rendering index (CRI) | 80 | Warm-up time to 60% light | 0.5 s |
| | | Power Factor (Fraction) | 0.9 |
| | | Voltage (Nom) | 120-277 V |
| | | UL Type | UL Type B |

Contractor-grade MainsFit (UL Type-B) T8

Temperature

| | |
|---------------------------|-----------------|
| Ambient temperature range | -20 °C to 45 °C |
| T-Case Maximum (Nom) | 70 °C |

Controls and Dimming

| | |
|----------|---------|
| Dimmable | Limited |
|----------|---------|

Mechanical and Housing

| | |
|----------------|----------|
| Bulb Finish | Frosted |
| Bulb Material | Glass |
| Product Length | 1,200 mm |
| Bulb Shape | T8 |

Approval and Application

| | |
|-----------------------|---|
| Energy Saving Product | Yes |
| Approval Marks | RoHS compliance UL certificate DLC compliance |

Application Conditions

| | |
|-------------------------------------|-----|
| can it be used in closed luminaires | Yes |
|-------------------------------------|-----|



Product Data

| | |
|---------------------------------|-------------------------------|
| Order product name | 14.5T8/CNG/48-835/MF17/G 25/1 |
| Full product name | 14.5T8/CNG/48-835/MF17/G 25/1 |
| Order code | 577767 |
| Material Nr. (12NC) | 929003474504 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677577766 |
| Numerator - Packs per outer box | 25 |
| EAN/UPC - Case | 50046677577761 |

Dimensional drawing

| Product | D1 | D2 | A1 | A2 | A3 |
|-------------------------------|---------|-------|------------|------------|------------|
| 14.5T8/CNG/48-835/MF17/G 25/1 | 25.7 mm | 28 mm | 1,198.2 mm | 1,205.3 mm | 1,212.4 mm |

Photometric data




General uniform lighting - 14.5T8/CNG/48-835/MF17/G 25/1

Spectral Power Distribution Colour - 14.5T8/CNG/48-835/MF17/G 25/1


Contractor-grade MainsFit (UL Type-B) T8

Photometric data





Light Distribution Diagram - 14.5T8/CNG/48-835/MF17/G 25/1

Lifetime



Life Expectancy Diagram - 14.5T8/CNG/48-835/MF17/G 25/1

Life Expectancy Diagram - 14.5T8/CNG/48-835/MF17/G 25/1




Lumen Maintenance Diagram - 14.5T8/CNG/48-835/MF17/G 25/1

Lumen Maintenance Diagram - 14.5T8/CNG/48-835/MF17/G 25/1

Contractor-grade MainsFit (UL Type-B) T8

Lifetime



Life Expectancy Diagram - 14.5T8/CNG/48-835/MF17/G 25/1

