


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	'A' DIA.	MOUNTING SCREW	WEIGHT lbs/100pcs (g)/100pcs	USE WITH ANY OF THESE CABLE TIES	CABLE TIE RETENTION FEATURE
TMEH2S5-_350	.20 (5.1)	#10 (M5)	.882 (400.9)	I, S, H, EH	NO
TMEH2S6-_350	.26 (6.6)	1/4" (M6)	.861 (391.2)	I, S, H, EH	NO
TMEH2S8-_350	.32 (8.2)	5/16" (M8)	.827 (375.7)	I, S, H, EH	NO



NOTES:

1. MATERIAL: NYLON 66, IMPACT MODIFIED, UV RESISTANT, HEAT STABILIZED
2. MAXIMUM APPLIED TORQUE IS 115 IN-LB FOR ALL MOUNTS

B

B

A

A

ANGLOBAL_SIZE

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
35B	02-22-24	BDK	JADE	DJSL	C. REMOVED REDUNDANT MATERIAL FROM TITLE BLOCK B. DIMENSION 0.54 WAS 0.53 A. DIMENSION 1.42 WAS 1.41	013073 r01

TITLE				HEAVY DUTY CABLE TIE MOUNT			
				CUSTOMER DRAWING			
ITEM REVISION NAME		00076SCA/35		PANDUIT			
DATASET FILE NAME		00076SCA_DC/35B					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				MATERIAL:			
.x ± .1 [2.54]		.xxx ± .005 [.127]		△ C SEE NOTES			
.xx ± .01 [.25]		ANGLES ± 5°		DRAWING NUMBER:			
				00076SCA_DC			
DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1		SIZE	
CWG	03/23/2017	FCHE	1:1			A	

2

1