

FEATURES & SPECIFICATIONS

INTENDED USE

For use with housings L7X, L7XR, LC6, L7XF and L7XFR.

CONSTRUCTION

Aluminum one piece reflector.

Polyester powder coat paint.

Anodized finishes have white integral flange ring as standard.

INSTALLATION

Socket to trim interface.

Retaining clips pull and snap onto top of reflector to hold trim inside housing.

LISTINGS

U.L. Listed to U.S. and Canadian safety standards.

Damp location listed.

WARRANTY

1-year limited warranty. Complete warranty terms located at www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

Actual performance may differ as a result of end-user environment and application.

Note: Specifications subject to change without notice.


Catalog Number
Notes
Type

6" Full Reflector Trim

702

OPEN

Narrow Flange




Specifications

Height: 6-1/8 (15.6)

Lamp opening: 5-7/8 (14.9)

Diameter: 7-5/8 (19.4)

All dimensions are inches (centimeters) unless otherwise indicated.



ORDERING INFORMATION

For shortest lead times, configure product using **bolded options**.

Example: 702A

702A	
Series	Finish ¹
702	A Clear diffuse
	AZ Clear specular

Accessories: Order as separate catalog number.	
CRT6	6" goof ring, white

Housing Compatibility: Housing and trim ordered separately.			
Application	Source	Maximum wattage	Housing
IC	Incandescent	75 PAR30	L7X, L7XR, LC6
		65 BR30	
	Fluorescent	13DTT	L7XF, L7XFR
		26TRT	

Notes

1 See [702-TOR](#) specification sheet for white finish.

702 6" Open Full Reflector Trim

For BR and PAR reflector lamps, see lamp manufacturer's published raw lamp data for photometrics.