# **Motor Protection**

Amp-Trap® and 9F60 Series

#### MEDIUM VOLTAGE FUSES

2.4kV, 2.54kV, 4.8kV, 5.08kV AND 7.2kV FERRULE MOUNTED FUSES





Mersen R-Rated fuses are current-limiting, high interrupting rating fuses intended for the short circuit protection of medium voltage motors and motor controllers. R-Rated fuses are back-up fuses that have a minimum interrupting rating, and must be coordinated with overload relays in combination motor starters. These fuses come with a 3 (size D) or 4 (size E) inch diameter barrels with ferrules and are mounted in spring reinforced clips. Used in and required for replacement in motor controllers by many major manufacturers.

#### FEATURES/BENEFITS:

- The Amp-Trap and 9F60 R-Rated fuses are UL Recognized.
- Ferrule mounting for standard clips and interchangeability with other brands of fuses.
- Current-limiting for superior equipment protection.
- Metal embossed catalog number and manufacturing date for lasting identification.
- Blown-fuse indicator to give positive identification of open fuse.
  - Amp trap: 3" Barrel 2 lb tripped force 0.50 Inch
  - 9F60: 0.125 lb tripped force 0.20 Inch
- Many parts offered in non-indicating versions for use in Class 1, Div 2 environments.
- Hook-eye option featured on some models for non-load break isolation by hookstick.
  - A051F part numbers include welded hook-eye feature and are designed for use in Eaton Ampgard MCC, and direct replacement for 5ACLS series Eaton fuses
  - Optional hook-eye is also available on A480 part numbers, factory installed.

# **Ratings:**

# **Amp-Trap**

#### A240R

Volts: 2.4kVAC
 Amps: 1 to 36R
 IR: 65kA Sym

#### **A480R**

Volts: 4.8kVACAmps: 2 to 36RIR: 64-65kA

#### A051F

Volts: 5.08kVAmps: 2 to 24RIR: 50kA Sym

#### A072F

Volts: 7.2kVACAmps: 2 to 24RIR: 65kA Sym

# 9F60 SERIES TYPE EJ-2

#### 9F60

• **Volts:** 2.54kVAC, 5.08kVAC

Amps: 2 to 36RIR: 50kA Sym

# **APPLICATIONS:**

 Short circuit protection of medium voltage motors and motor controllers.

# APPROVALS:



• Amp-Trap: UL File E93367

9F60: UL File E191980

#### **DEFINITIONS:**

**R-Rating:** R-Rated fuses are back-up fuses that operate as follows (Per IEEE C37.42-2016): An R-Rated fuse will melt in the range of 15 to 35 seconds at a value of current equal to 100 times the "R" rating.

**Back-up Current-Limiting Fuses:** A back-up current-limiting fuse is a fuse that can interrupt any current between its rated minimum interrupting current and its maximum interrupting current. Back-up fuses are not designed or intended to open under overload conditions.

**Continuous Ampere Rating at 40°C:** The continuous amp rating defines the thermal capability of the fuse per IEEE C37.42-2016 and should not be the sole factor in fuse selection.

# 2.4kV FERRULE MOUNTED FUSES:

# 2.4kV R-Rated Amp-Trap Series

7.5" (191 mm) Clip Centers - Barrel diameter size D (3")



<sup>\*\*</sup> Not recommended for use in fuse clips which grasp only one barrel.

#### 2.4kV / 2.54kV Ferrule mounted fuses:

Indicator Flush with Surface

# 2 Lb. Force (Tripped)




Figure A




Figure B




Figure C




# 2.4kV AND 5.08kV FERRULE MOUNTED FUSES:


# 2.4kV R-Rated 9F60 EJ-2 Series

7" (179 mm) Clip Centers - Barrel diameter size D (3")



Catalog No.		Continuous Amp rating at 40°C	Minimum Interrupting Rating RMS Amp	No of Barrels	Fig.	Indicating	Dimension L Inches (mm)	1 Phase interrupting rating	
	Size							UL Component Recognition Max IR RMS Sym	Max Voltage Tested  Max IR RMS Sym
9F60LCB502	2R	70	195	1	D	Yes	10.88 276)	50kA at 2.54kV	50kA at 2.54kV
9F60LCB503	3R	100	270						
9F60LCB504	4R	130	370						
9F60LCB506	6R	170	580						
9F60LCB509	9R	200	820						
9F60LCB512	12R	230	1150						
9F60MCB518	18R	390	1800	2	Е				
9F60MCB524	24R	450	2400	2					
9F60LCL302	2R	70	195	1	D	No	10.88 (276)	50kA at 2.54kV	50kA at 2.54kV
9F60LCL303	3R	100	270						
9F60LCL304	4R	130	370						
9F60LCL306	6R	170	580						
9F60LCL309	9R	200	820						
9F60LCL312	12R	230	1150						
9F60MCL318	18R	390	1800	2	Е				
9F60MCL324	24R	450	2400						





# 5.08kV R-Rated 9F60 EJ-2 Series

12" (305 mm) Clip Centers - Barrel diameter size D (3")

Catalog No.		Continuous Amp rating at 40°C	Minimum Interrupting Rating RMS Amp	No of Barrels	Fig.	Indicating	Dimension L Inches (mm)	1 Phase interrupting rating	
	Size							UL Component Recognition Max IR RMS Sym	Max Voltage Tested Max IR RMS Sym
9F60LJD502	2R	70	195	1	D*	Yes	15.97 (406)	50kA at 5.08kV	50kA at 5.08kV
9F60LJD503	3R	100	270						
9F60LJD504	4R	130	370						
9F60LJD506	6R	170	580						
9F60LJD509	9R	200	820						
9F60LJD512	12R	230	1150						
9F60MJD518	18R	390	1800	2	E*				
9F60MJD524	24R	450	2400						
9F60LJN302	2R	70	195	1	D*	No	15.97 (406)	50kA at 5.08kV	50kA at 5.08kV
9F60LJN303	3R	100	270						
9F60LJN304	4R	130	370						
9F60LJN306	6R	170	580						
9F60LJN309	9R	200	820						
9F60LJN312	12R	230	1150						
9F60MJN318	18R	390	1800	2	E*				
9F60MJN324	24R	450	2400						