



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



A

B

PANDUIT * PART NO.	USE WITH ANY OF THESE CABLE TIE CROSS-SECTIONS	WEIGHT lbs/ 100 pcs. (g)	SCREW SIZE
LPMS-S8	MINIATURE INTERMEDIATE STANDARD	0.102 (46.3)	#8 (M4)



NOTES:

* 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND COLOR.

2) MATERIAL:
MATERIAL IS NATURAL NYLON 6/6.
PART NUMBERS ENDING IN "20" ARE BLACK

02B	9/14/2023	RVU	JEFP	MSAD	C. REMOVED -S FROM TITLE. B. REMOVED QTY. COLUMN. A. REMOVED PN SUFFIX, -C AND -M FROM TABLE.	GAECN06908
02A	7/14/2023	RVU	JEFP	MSAD	G. UPDATED NOTE 2. F. ADDED ALL REF. DIMENSIONS EXCEPT SLOT WIDTH, SLOT DEPTH, AND HOLE. E. ADDED DIMENSION SLOT DEPTH, 0.058 +/- .005 [1.5 +/- 0.127]. D. 0.225 +/- .010 [5.7 +/- 0.127] WAS 0.230 [5.8]. C. ADDED 'P' LOGO ON THIS MODEL. B. REMOVED 0.550 [14.0] AND 0.250 [6.4] DIMENSIONS. A. REMOVED 0.184 [4.67] / 0.164 [4.2] DIA. X 82° COUNTERSINK HOLE REF.	GAECN06755
2	3/10/2020	RVU	DJW	JHAC	REBUILD MODEL AND RECREATE. Remove material "-0 weather resistant black nylon 6.6". CHANGE NOTE 2, MATERIAL -20 BLACK NYLON 6/6.	GAECN05597
1	2/1/06	JAD			ADDED NOTE 2, 0.74 (REF.) WAS 0.75, 0.184 / 0.164 WAS 0.180 / 0.164.	GB0239HG
R	6/6/01	LGG			REVISED DRAWING FROM SS-5783-A-RV 3 TO NEW DRAWING NUMBER.	GB0239HG

TITLE		CUSTOMER DRAWING	
LOW PROFILE MOUNT LPMS		PANDUIT	
ITEM REVISION NAME		G03597HS/02	
DATASET FILE NAME		G03597HS_DC/02B GB0239HG CUST DWG	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± - .xxx ± .020 [.5]		SEE NOTE 2	
.xx ± - ANGLES ± -		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		GB0239HG	
DRAWN BY	DATE	CHK	SCALE
LGG	6/6/01	JHAC	NONE
SHT 1 OF 1			SIZE
			A

C

A