

Project:		Type:
Drawn by:	Catalogue #:	Date:

FL

MINI FLOOD

The FL series is a family of highly efficient and affordable compact flood lights available in four different lumen packages. Each fixture has a modern thin design with an aluminum housing and comes standard with a black powder coat finish. Typical applications include both commercial and residential environment: backyards, walkways as well as flood lighting of signs and building fronts.

FEATURES AND SPECIFICATIONS

Construction

Housing

Aluminum housing comes standard in a black powder coat finish.

Mounting options

The fixture comes with either a knuckle mount or a yoke mount.

Lens

Tempered glass lens is standard in this product series.

Electrical

- The drivers allow input from 120 V and is reliable in the coldest of temperatures
- The FL flood is suitable for ambient temperature range of -40°C to +50°C. Available in 4 000 K color temperature with a lumen per watt ratio of 110 lm/W to 117 lm/W depending on the lumen package.

• Compliances

- IP65
- Wet location
- Meets requirements of ICES-005 issue 5 for class B products
- cETLus



















Intertek







OVERVIEW

Light source	LED
Watts (W)	19 - 51
Lumen output (lm)	1 870 - 5 674
Efficacy (Im/W)	99 - 117
Color temperature (K)	4 000
CRI	70 - 80

FL • Rev. 4/1/2023




QUICK SHIP AND TECHNICAL SPECIFICATION TABLE : 1

Order code	Model number	Watts (W)	Volts (V AC)	Color temp. (K) ²	Lumen output (Im) ³	Efficacy (Im/W)	CRI	Beam angle (°)	Finish	LED current (mA)	Power factor	THD (%)		al equivalent (W) HPS	Case qty (master)
68383	FL/S2/20W/40K/KN/BK/CHOICE/STD	20	120	4 000	2 313	117	70	120	Black	66	0.98	22	100	70	40
68213	FL/S2/30W/40K/KN/BK/CHOICE/STD	30	120	4 000	3 207	110	70	120	Black	115	0.97	23	100	100	20
68211	FL/S2/50W/40K/KN/BK/CHOICE/STD	50	120	4 000	5 674	112	70	120	Black	92	0.98	21	175	150	20
68212	FL/S2/50W/40K/YK/BK/CHOICE/STD	50	120	4 000	5 674	112	70	120	Black	92	0.98	21	175	150	20


¹ QUICK SHIP: Product availability is subject to change without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

DIMENSIONS

KNUCKLE MOUNT



YOKE MOUNT



Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.

² Typical color temperature range: +/- 5 %.


³ Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.



PHOTOMETRIC DATA¹

68383 • FL/S2/20W/40K/XX/BK/CH0ICE/STD • 2 060.6 lm


Polar candela distribution



Zonal lumen summary


Zone	Lumens	% Fixture				
0-30	608.6	29.6%				
0-40	994.5	48.8%				
0-60	1 744.0	85.1%				
60-90	316.7	14.9%				
0-90	2 060.6	100%				

Illuminance at a distance



68213 • FL/S2/30W/40K/XX/BK/CHOICE/STD • 3 040.1 Im

Polar candela distribution



Zonal lumen summary


Zone	Lumens	% Fixture
0-30	899.4	29.6%
0-40	1 484.0	48.8%
0-60	2 588.6	85.1%
60-90	451.5	14.9%
0-90	3 040.1	100%

Illuminance at a distance

	Center beam fc		Beam width		
17.0'	3.95		42.0'	52.1'	
34.01	0.99		84.0'	104.2'	
51.0'	0.44		126.0'	156.3'	
68.01	0.25		168.1'	208.41	
85.0¹	0.16		210.1'	260.5'	
102.0¹	0.11		252.1'	312.6'	
	Vert. spread: Horiz. spread:	102.0° 113.7°			

68211 & 68212 • FL/S2/50W/40K/XX/BK/CH0ICE/STD • 5 250.8 Im


Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture				
0-30	1 486.5	28.3%				
0-40	2 465.0	46.9%				
0-60	4 401.7	83.8%				
60-90	849.1	16.2%				
0-90	5 250.8	100%				

Illuminance at a distance



Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.



¹ Complete IES files available on our website.