



FXSD51

By Killark
Catalog # [FXSD51](#)

XSD/XSX/FXSD/FXSX Series - FXSD Single Gang Aluminum Manual Motor Starting Switch - 1 Pole Single Phase - Feed-Thru - Hub Size ¾ In.



*Representative Image

Features

- Motor running protection when overload heaters are used.
- Factory Sealed so no external seals are required.
- Type 3 (raintight) rated.
- Enclosures are cast copper-free aluminum alloy.
- Operating shaft is stainless steel.
- Multiple gang assemblies available in combination with pilot lights, pushbuttons and switches on request.
- Ground flange joint between bolted cover and box provide required flame path.
- Provisions for padlocking switch in either “ON” or “OFF” position is standard.

General

EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	1
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	FXSD
Type	
UPC	783936197371

Dimensions

Dimensions	8.25 in x 5.875 in x 6.875 in
Gross Weight with Packaging	4.47
Height	6.875 in
Length	8.25 in
Width	5.875 in

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	230 V

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups C, D• Class I, Zones 1 & 2, Groups IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2

Nema Rating	3
UL File Number	E53360 / E12379

Product Assets

[Catalogs - Killark Catalog](#)
[Certifications - FXS & XS Series Motor Starters UL Certification](#)
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.