

Project: _____ Type: _____

Drawn by: _____ Catalogue #: _____ Date: _____

Individual Spec Sheet

T8 - BALLAST COMPATIBLE 3 CCT SELECTABLE LED LINEAR TUBES

ORDERING INFORMATION

Order code: 69893
Model number: T8/13W/80/3CCT/48/STD/SMX
UPC: 069549031135
Case quantity: 25
DLC Unique ID: S-WZFCHM

PHYSICAL DATA

Dimensions mm (in): 1 219 (48)
Shape: T8
Base: G13
Material: Housing: Plastic, Lens: Glass (frosted), PET coating

PERFORMANCE DATA

Bare Lamps Watts (W): 13
Volts (VAC): 120-277/347V
Color temperature (K)¹: 3 500/4 000/5 000K
Lumen output (lm)²: 2 150
Efficiency (lm/W): 134
CRI: >80
Life L70 (h)³: 50 000
Beam angle (°): 180
Dimming: Depends on the ballast
Power Factor: >0.9
Frequency (Hz): 60
Operating temp. range: -20°C/ -4°F to 45°C/ 113°F
Installation method: Ballast compatible
Application (indoor/outdoor): Indoor

¹ Typical color temperature range: +/- 5 %.

² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.

³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations.


LUMEN SPECIFICATION TABLE

Order code	Average System Watts (W)			Initial Lumens (lm)*		
	LBF	NBF	HBF	LBF	NBF	HBF
69893	13	16	22	1 745	2 150	2 660

ADDITIONAL INFORMATION

Direct replacement for 32W/48T8, 30W/48T8, 28W/48T8, 25W/48T8 only.

DIMENSIONS AND WEIGHT



This lighting equipment meets requirements of ICES-005 issue 5 class A for use in commercial applications. Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.



enclosed
fixture

