PHILIPS ADVANCE

LED Driver

Xitanium

180W 0.1-1.25A 0-10V Dimming with SimpleSet and Aux. Output XI180C125V200PSF1












Philips Advance Xitanium LED drivers with SimpleSet technology and auxiliary power supply extend the driver application scope to include simple self-contained control solutions for luminaires. The driver provides an additional auxiliary output for powering simple sensors (occupancy/photocell), and the driver has a built-in standby mode through the 0-10V leads. The additional auxiliary power output eliminates the need for a mains relay or power pack for the sensor and allows the sensor to turn the driver on/off and also operate the dimming function.


Specifications

Input Voltage (Vac)	Output Power (W)	Output Voltage (V)	Output Current (A)	Efficiency@ Max. Load and 75°C Case	Max. Case Temp. (°C)	Input Current (A)	Max. Input Power (W)	THD @ Max. Load (%)	Power Factor @ Max. Load	Surge Protection (Combi- Wave, KV)	Envir. Protection Rating
120	180 70-210	/O-210	91	Life - 85°C	1.87	200	200 <10%	-100/	<10% >0.95	6	UL damp & dry
277	160	70-210	0.1 - 1.25	93	UL - 90°C	0.72	200	<10 %	Z0.95	0	and Type HL

Enclosure

	In. (mm)
Case Length (L2)	8.31 (211.0)
Case Width (W)	2.31 (58.0)
Case Height (H)	1.48 (37.6)
Mounting Length (M)	8.91 (226.2)
Overall Length (L1)	9.45 (240.0)
Center of SimpleSet Antenna (L3)	3.75 (95.3)





Dimming	Dimming Range (with specified dimmers)	Minimum Output Current (A)	
0-10V Analog Class 1 and 2 Wiring	10% ~ 100%	0.07	

Features

- · 50,000+ hour lifetime¹
- Programmable output current through SimpleSet technology
- · Large operating window
- 6kV combi-wave surge rating to comply with ANSI C82.77-5 CAT C low
- · Auxiliary power output
- · 0-10V dimming with ON/OFF functionality

Benefits

- · Enables long life luminaire designs
- · Fast and simple way of programming
- Enables fixture designs with wide variety of loads and adjustable current options
- No external surge protection required to pass C82.77-5 CAT C low
- Provides power supply for additional control/sensing devices in the fixture
- The driver can be turned ON/OFF using a passive low-voltage control device or relay

Application

- · Area
- · Roadway
- Parking garages
- · Floodlights
- · High-bay and mid-bay

Electrical Specifications

All the specifications are typical and at 25°C Tcase unless specified otherwise.

Product Data

Order Information					
Full Product Code	XI180C125V200PSF1M (Mid-Pack, 10pcs/Box)				
Line Frequency	50/60Hz				
Min. Mains Voltage Operational	108 Vac				
Max. Mains Voltage Operational	305 Vac				
Output Information					
Maximum Open Circuit Voltage	285Vdc				
Output Current Ripple	15% max @ max lout				
(ripple = peak to average / average)	(Low frequency ripple (≤120Hz) content <5%)				
Output Current Tolerance	<5%				
(in performance window)					
Protections	Short Circuit, Open Circuit Protection for LED + and LED – and				
	Temperature Foldback				
Features					
Auxiliary Power Supply Output					
Nominal Aux. Output Voltage 16 – 24Vdc					
Maximum Aux. Output Voltage Ripple (peak/average)	2%				
Rated Aux. Output Power	2.5W				
Peak Power (<10s)	4W				
Max. Output Current	140mA. See Aux. Output for details.				
Turn-on Time (from power on to >16V)	<100ms				
Turn-off Time (from power off to <1V)	<1s				
Max. Voltage Overshoot during Turn ON	30Vdc				
Max. Voltage Undershoot during Turn ON	8Vdc				
Max. Hold-up Time after Mains Power OFF (20mA load)	t.b.d				
Protections	Short Circuit & Open Circuit Protection for Aux. + and Aux. – and				
	Over-temperature Foldback				

l. Philips Advance Xitanium LED drivers are manufactured to engineering standards correlating to a designed and average life expectancy of 50,000 hours of operation at maximum rated case temperature. Minimum 90% survivals based on MTTF modeling.

Electrical Specifications

All the specifications are typical and at 25°C Tcase unless specified otherwise.

Product Data (continued)

0-10V Dimming Interface					
Dimming Source Current	100-250μA (for dimming voltage >1V)				
0-10V Active Range	1V to 8V. See dim curve for details.				
0-10V Turn OFF Threshold	<0.3V				
0-10V Turn ON Threshold	>0.7V				
Input Standby Power in OFF State (across 120-277V mains range)	< 0.5W ²				
Protections	Short Circuit & Open Circuit Protection for Dim + and Dim – and protected against accidental mains applied on dimming input				
Programmable Features					
AOC (adjustable output current)	0.1A-1.25A via SimpleSet (Factory Default at 1.05A)				
Additional Configurable Features	Adjustable Min. Dim Level, Adjustable Lumen Output, Adjustable Lumen Output Min., OEM Write Protection Switch Aux. output ON/OFF				
Environment & Approbation					
Operating Ambient Temp. Range	-40°C to +55°C				
Max. Case Temperature (Tcase)	90℃				
Agency Approbations	UL 8750, CSA 250.13				
Electromagnetic Compliance	FCC Title 47 Part 15 Class A				
Audible Noise	<24dB Class A				
Weight	2.1 Lbs / 0.95 kgs				

Electrical Specifications


All the specifications are typical and at 25°C Tcase unless specified otherwise.

0-10V Dimming


Dimming source current from the driver: 100-250uA (@ 0<Vdim<8V)

Minimum dim level: 10% of lout setting as default Maximum output voltage on the dimming wires: 12V

0-10V Dimming Curve




Detail on Hysteresis for ON-OFF



Electrical Specifications

All the specifications are typical and at 25°C Tcase unless specified otherwise.

Driver Output Window




Notes

- 1. Factory default output current is 1.05A.
- 2. To get a 100% to 10% dimming range, the output current setting through AOC should be \geq 700mA.
- 3. Factory default minimum dimming level is 10%. This can be adjusted between 10% and 100% using Philips MultiOne.

Electrical Specifications

All the specifications are typical and at 25°C Tcase unless specified otherwise. Chart represents a normalized load regulation of the auxiliary power supply. Nominal ratings are listed on page 2.


Auxiliary Power



Electrical Specifications

All the specifications are typical and at 25°C Tcase unless specified otherwise.


Output Current Vs. Driver Case Temperature



Note

There is ±5°C tolerance on the driver case temperature.


Driver Lifetime Vs. Driver Case Temperature




Performance Characteristics

Based on measurements on a typical sample at 75°C case. The accuracy of the measurements is within the tolerance of the measurement instruments. Measurements were made with no load on the auxiliary output port.

Efficiency Vs. Output Voltage at 120Vac




Efficiency Vs. Output Voltage at 277Vac




Performance Characteristics

Based on measurements on a typical sample at 75°C case. The accuracy of the measurements is within the tolerance of the measurement instruments. Measurements were made with no load on auxiliary output port.


Power Factor Vs. Output Power



Total Harmonic Distortion (THD) Vs. Output Power



Inrush Current Info



Vin	lpeak	T (@ 10% of Ipeak)	
120 Vrms	66 A	247 µS	
277 Vrms	158 A	242 μS	

Inrush current is measured at peak of the corresponding line voltage. Source impedance per NEMA 410.

Lightning Surge Info

ANSI Surge Type	Differential Mode (L-N)	Common Mode (L-G, N-G, L&N-G)
1.2/50 μ s Combination Wave (w/t 2 Ω)	6kV	6kV

Isolation

Isolation	Input	Output	0-10V	Aux. Output	Enclosure
Input	NA	2xU+1kV	2.5kV	2.5kV	2xU+1kV
Output	2xU+1kV	NA	2.5kV	2.5kV	2xU+1kV
0-10V	2.5kV	2.5kV	NA	NA	2.5kV
Aux. Output	2.5kV	2.5kV	NA	NA	2.5kV
Enclosure	2xU+1kV	2xU+1kV	2.5kV	2.5kV	NA

U = Max. input voltage





Philips Lighting North America Corporation 10275 W. Higgins Road, Rosemont IL 60018 Tel: 800-322-2086 Fax: 888-423-1882 Customer/Technical Service: 800-372-3331 OEM Support: 866-915-5886

Philips Lighting Canada Ltd. 281 Hillmount Rd, Markham, ON, Canada L6C 2S3 Tel. 800-668-9008