



PL-C Cluster 4-Pin Base

PL-C 26W/841/4P/ALTO 10PK

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G24q-3
Light Technical	
Color Code	841 [CCT of 4100K]
Luminous Flux	1,800 lm
Color Designation	Cool White (CW)
Luminous Efficacy (rated) (Nom)	67 lm/W
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	26.0 W


Lamp Current (Nom)	0.335 A
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	29 kWh
Product Data	
Order product name	PL-C 26W/41/4P/ALTO 10PK
Full product name	PL-C 26W/841/4P/ALTO 10PK
Order code	383372
Material Nr. (12NC)	927907384030

PL-C Cluster 4-Pin Base

Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.133 lb
EAN/UPC - Product/Case	046677111779
Numerator - Packs per outer box	10


EAN/UPC - Case	60046677111771
----------------	----------------

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-C 26W/41/4P/ALTO 10PK	1-1/16 inch	1-1/16 inch	5-3/16 inch	5-7/8 inch	6-1/2 inch

Photometric data




Spectral Power Distribution Colour - PL-C 26W/41/4P/ALTO 10PK

Lifetime



Life expectancy diagram - 3 hour cycle



Life expectancy diagram - 12 hour cycle

PL-C Cluster 4-Pin Base

Lifetime



Lumen Maintenance Diagram - PL-C 26W/41/4P/ALTO 10PK

