



# Pulse Start Metal Halide Standard

## MS750/BU/PS 6PK

Philips Pulse Start Metal Halide Lamps offer an optimized metal halide system for greater efficiency and lumen maintenance.

### Warnings and Safety

· R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

### Product data


General Information		Warm-up time to 60% light	
Cap-Base	E39 [Single Contact Mogul Screw]		<180 s
Light Technical		Controls and Dimming	
Luminous Flux	53,300 lm	Dimmable	No
Color Designation	4000 Kelvin	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	109 lm/W	Bulb Finish	Clear
Chromaticity Coordinate X (Nom)	0.385	Bulb Material	Hard Glass
Chromaticity Coordinate Y (Nom)	0.4	Bulb Shape	BT37
Correlated Color Temperature (Nom)	4000 K	Approval and Application	
Luminous Efficacy (Rated) (Min)	98 lm/W	Mercury (Hg) Content (Max)	125 mg
Color rendering index (CRI)	>65	Product Data	
Operating and Electrical		Order product name	MS750/BU/PS 6PK
Power Consumption	750 W	Full product name	MS750/BU/PS 6PK
Wattage Equivalent	750 W		

## Pulse Start Metal Halide Standard

Order code	135400
Material Nr. (12NC)	928601179101
Numerator - Quantity Per Pack	1
Net Weight (Piece)	1.000 g
EAN/UPC - Product/Case	046677135409

Numerator - Packs per outer box	6
EAN/UPC - Case	50046677135404

### Dimensional drawing



Product	D (max)	C (max)
MS750/BU/PS 6PK	122 mm	282 mm

