



# Reflector Infrared BR40, PAR38

## 250BR40 IR/1 120V 4/1


Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Philips Infrared lamps are suited for heating and drying in industrial and commercial applications. These incandescent, gas-filled infrared heat lamps come up to full temperature almost immediately, eliminating costly warm-up time. Highly efficient heat generators that produce a minimum of light rays and a high amount of infrared radiation. The BR40 lamp provides a built-in reflector for radiant energy control.

### Product data

General Information		Bulb Material	
Cap-Base	E26 [Single Contact Medium Screw]	Bulb Material	Hard Glass
Operating Position	UNIVERSAL [Any or Universal (U)]	Bulb Shape	BR40
Nominal lifetime	5,000 hour(s)	<b>Product Data</b>	
Rated Lifetime (Hours)	5,000 hour(s)	Order product name	250BR40 IR/1 120V 4/1
Lighting Technology	Incandescent	Full product name	250BR40 IR/1 120V 4/1
<b>Operating and Electrical</b>		Order code	203836
Power Consumption	250 W	Material Nr. (12NC)	925255136308
Wattage Equivalent	250 W	Numerator - Quantity Per Pack	1
Voltage (Nom)	120 V	Net Weight (Piece)	0.088 kg
<b>Controls and Dimming</b>		EAN/UPC - Product/Case	046677203832
Dimmable	No	Numerator - Packs per outer box	4
<b>Mechanical and Housing</b>		EAN/UPC - Case	50046677203837
Bulb Finish	Clear		

## Reflector Infrared BR40,PAR38

### Dimensional drawing



Product	D	C (max)
250BR40 IR/1 120V 4/1	125 mm	174.6 mm

