

Project:	
Fixture Type:	
Location:	
Contact/Phone:	

6" TC 900 LUMEN LED DOWNLIGHT NEW CONSTRUCTION

TC22LED (G4 09LM) RECESSED HOUSING





OPEN TRIMS

PRODUCT DESCRIPTION

Dedicated LED new construction housing with integral light engine \bullet Shallow housing allows for fit in 2 x 6 construction \bullet TC housing design for use in non-insulated areas \bullet If installed where insulation is present, the insulation must be pulled back 3" from all sides of the TC housing \bullet LED housing is designed to provide 50,000 hours of life and is compatible with many standard Juno trims \bullet 5 year limited warranty on LED components.

ENVIRONMENTALLY FRIENDLY, ENERGY EFFICIENT

- No harmful ultraviolet or infrared wavelengths
- No lead or mercury
- Comparable light output to 26W compact fluorescent while consuming only 18W*

PRODUCT SPECIFICATIONS

LED Light Engine LED array integrated to one piece high purity aluminum, thermally conductive housing provides uninterrupted heat transfer to ensure long life of the LED • Replaceable light engine mounts directly to housing and incorporates the latest generation, high lumen output LED array • LEDs are binned within a 3-Step MacAdam Ellipse exceeding ENERGY STAR® requirements yielding superior fixture to fixture color uniformity • 2700K, 3000K, 3500K or 4000K color temperatures available • 90 CRI minimum.

Optical System Computer-optimized reflector design with high reflectance white finish coupled with a high transmission diffusing lens conceals the LEDs and produces uniform aperture luminance \bullet Deep regression of lens produces a low glare, efficient system that can produce over 900 lumens with select trims using less than $17W^* \bullet$ Wide flood (>70°) distribution shipped as standard with optional optic accessories available and sold separately.

Aesthetic Trim Selections Compatible with wide selection of existing Juno trims • Shadow free, knife edge design blends seamlessly into ceiling.

LED Driver Universal voltage drivers that accommodate input voltage from 120-277 volts AC at 50/60Hz are available and dimmable with the use of most 0-10V dimmers • Power factor > 0.9 at 120V input • Optional Lutron Hi-Lume® A-Series driver accommodates 120-277 volts AC at 50/60Hz • Mounted between the j-box and housing for easy access and cool operation • For a list of compatible dimmers, see JUNOTCLED-DIM.

Emergency Battery Option Battery factory assembled to housing with remote mounted test switch included • Drives LED array for 90 minutes to meet Life Safety Code (NFPA-LSC), National Electrical Code (NEC) and UL requirements • Provides 50% light output in emergency mode.

Life Rated for 50,000 hours at 70% lumen maintenance.

Labels ENERGY STAR® Certified when used with select baffle and cone trims

- UL listed for U.S. and Canada through-branch wiring, damp locations
- Union made UL and cUL listed.

Testing All reports are based on published industry procedures; field performance may differ from laboratory performance.

Specifications subject to change without notice.

HOUSING FEATURES

Housing Designed for use in TC applications (non-insulated) • Aluminum housing • Housing is vertically adjustable to accommodate up to a 2" ceiling thickness.


Junction Box Pre-wired junction box provided with (5) ½" and (1) ¾" knockouts and ground wire, UL listed and cUL listed for through-branch wiring, maximum 8 No. 12 AWG 90° C branch circuit conductors (4 in, 4 out) • Junction box provided with removable access plates • Knockouts equipped with pryout slots.

Mounting Frame 16-gauge galvanized steel mounting ring equipped with vertically adjustable mounting brackets that accept ½" conduit or "C" channels (HB26 or HB50), linear flat bars (LB27) or Patented (US Patent D552,969) Real Nail® 3 bar hangers (HB1).

*Nominal input wattage with universal voltage driver under stable operating conditions

DIMENSIONS





67/8" CEILING CUTOUT

ELECTRICAL DATA

STANDARD UNIVERSAL VOLTAGE DRIVER

(MVOLT EZ10, MVOLT ZT10, MVOLT EZ1 and MVOLT ZT1)

	120V	277V
Input Power	16.1W (+/-5%)	16.9W (+/-5%)
Input Current - Max	0.14A	0.06A
Frequency	50/60Hz	50/60Hz
EMI/RFI	FCC Title 47 CFR, Part 15,	FCC Title 47 CFR, Part 15,
	Class B (residential)	Class B (residential)
Minimum starting temp	-20°C (-40°F)	-20°C (-40°F)

UNIVERSAL VOLTAGE DRIVER WITH EMERGENCY OPTION (MVOLT ZT10 BR, EZ10 BR, ZT1 BR and EZ1 BR)

	120V	277V
Input Power	18.9W (+/-5%)	19.6W (+/-5%)
Input Current - Max	0.16A	0.07A
Frequency	50/60Hz	50/60Hz
EMI/RFI	FCC Title 47 CFR, Part 15,	FCC Title 47 CFR, Part 15,
	Class A (Commercial)	Class A (Commercial)
Minimum starting temp	0°C (32°F)	0°C (32°F)

LUTRON HI-LUME® LED DRIVER (ECOD)

LOTKON THELOME	LLD DRIVER (LCCD)	
	120V	277V
Input Power	17.8W (+/-5%)	17.8W (+/-5%)
Input Current - Max	0.15A	0.06A
Frequency	50/60Hz	50/60Hz
EMI/RFI	FCC Title 47 CFR, Part 15, Class A (Commercial)	FCC Title 47 CFR, Part 15, Class A (Commercial)
Minimum starting temp	0°C (32°F)	0°C (32°F)



6" TC 900 LUMEN LED DOWNLIGHT NEW CONSTRUCTION

TC22LED (G4 09LM) RECESSED HOUSING

OPEN TRIMS

ORDERING INFORMATION Housing and trim can be ordered together or separate, but will always ship separately.

Example: TC22LED G4 O9LM 27K 90CRI MVOLT ZT BR

Series		Gene	ration	Lumens		Color	Temperature	CRI		Voltage/Drive	1
TC22LED	6" LED Downlight Non-IC Rated	G4	Generation 4	09LM	900 Nominal Lumens	27K	2700K	90CRI	90+ CRI	MVOLT ZT10	Multi-Volt (120-277), 0-10V, 10% dim
	Housing					30K	3000K			MVOLT ZT1	Multi-Volt (120-277), 0-10V, 1% dim
						35K	3500K			MVOLT EZ10	Multi-Volt (120-277), eldoLED 0-10V, 10% dim
						40K	4000K			MVOLT EZ1	Multi-Volt (120-277), eldoLED 0-10V, 1% dim
										MVOLT ECOD [†]	Multi-Volt (120-277), Lutron Hi-Lume EcoSystem, 1% Dimming

Emer	gency Battery	Territ	tory
BR†	Emergency Battery	CP	Chicago Plenum

 $\dagger : \text{MVOLT ECOD}$ and BR Emergency Battery not ENERGY STAR® certified Note: Chicago Plenum (CP) is not available with emergency option (BR) Note: Lutron driver (MVOLT ECOD) is not available with emergency battery pack (BR)



Trim/Description



6" Decorative Luminous Frosted Collar Trim - Luminous Collar (Frosted)

Trim Size: 24, 27, 9324, 9524 - 7 5/8" O.D.; 9702 - 7 3/4" O.D.; 9024 - 8" O.D. Alzak is a registered trademark of Alcoa Corp. Note: In Canada when insulation is present, Type IC fixtures must be used.

Notes: 1 Not ENERGY STAR® Certified.

9702

Accessories (ordered separately)

Catalog Number	Description	
HB1	Two 13 1/2" - 25" Real Nail® 3 bar hangers	
HB26	Two 26" C-channel bar hangers	
HB50	Two 50" C-channel bar hangers	
LB27	Two 27" linear bar hangers	
LEDOPTICG3 MFL	Medium Flood Optic (50°)	
LEDOPTICG3 NFL	Narrow Flood Optic (37°)	
LEDOPTICG3 SP	Spot Optic (10°)	
TR6 BRZ ²	6" Trim Ring - Bronze	
TR6 BL ²	6" Trim Ring - Black	
TR6 SC ²	6" Trim Ring - Satin Chrome	
TR6 WH ²	6" Trim Ring - White	

² Trim ring compatible with 24 and 27 trims.

6" TC 900 LUMEN LED DOWNLIGHT NEW CONSTRUCTION

TC22LED (G4 09LM) RECESSED HOUSING


OPEN TRIMS

PHOTOMETRICS

PHOTOMETRIC REPORT

Test Report #: PT02141401R Catalog No: TC22LED G4 09LM 35K 90CRI MVOLT with 24 WWH White Trim and Standard Wide Flood Optic

Luminaire Spacing Criterion: 1.16 Luminaire LPW: 70



CANDLEPOWER DISTRIBUTION

(Canaela	(Canaelas)			
Degrees				
Vertical	0°			
0	701			
5	694			
15	653			
25	583			
35	457			
45	207			
55	91			
65	45			
75	26			
85	6			
90	0			
Multiplier: 27k	′ - 0 93			

AVERAGE INITIAL FOOTCANDLES

Multiple Units (Square Array, 60'x60' room) Ceiling 80% Wall 50% Floor 20%

RCR1	RCR3	RCR5
76	63	52
49	40	33
34	28	23
27	23	19
22	18	15
17	14	11
12	10	8
	76 49 34 27 22 17	76 63 49 40 34 28 27 23 22 18 17 14

ZUNAL	LOMEN	30MM	AKI
Zone	Lumens	%Lamp	%Fixture
0-30°	517	N/A	46.0
0 - 40°	797	N/A	70.8
0-60°	1046	N/A	92.9
0 - 90°	1125	N/A	100.0

INITIAL FOOTCANDLES

(One Unit, 16.1W, 78.8° Beam)

Distance to Illuminated Plane (Feet)	Footcandles Beam Center	Beam Diameter
4	43.8	6.6'
6	19.5	9.9'
8	10.9	13.1′
10	7.0	16.4′


LUMINANCE (Average cd/m²)

	Average 0°	
Degrees	Luminance	
45	16031	
55	8676	
65	5788	
75	5507	
85	3774	

PHOTOMETRIC REPORT

Test Report #: LTL25975R Catalog No: TC22LED G4 09LM 35K 90CRI MVOLT with 27 CWH Clear Alzak® Trim and Standard Wide Flood Optic

Luminaire Spacing Criterion: 0.78 **Luminaire LPW: 77**



CANDLEPOWER DISTRIBUTION (Candelas)

30K - 0.99 40K - 1.01

Degrees	
Vertical	0°
0	1226
5	1151
15	874
25	685
35	477
45	222
55	74
65	15
75	0
85	0
90	0
Multiplier: 27	K - U 03

30K - 0.99 40K - 1.01

AVERAGE INITIAL FOOTCANDLES Multiple Units (Square Array, 60'x60' room)

Ceiling 80°	% Wall 50	0% Floor 2	0%
Spacing	RCR1	RCR3	RCR5
4.0′	78	71	61
5.0′	50	45	39
6.0′	35	32	27
7.0′	28	26	22
8.0′	22	20	17
9.0′	17	15	13
10.0′	12	11	10

ZONAL LUMEN SUMMARY

Zone	Lumens	%Lamp	%Fixture
0 - 30°	665	N/A	53.9
0 - 40°	967	N/A	78.3
0-60°	1218	N/A	98.7
0 - 90°	1234	N/A	100.0

INITIAL FOOTCANDLES

(One Unit, 16.1W, 58.1° Beam)

Distance to Illuminated Plane (Feet)	Footcandles Beam Center	Beam Diameter
4	76.6	4.4'
6	34.0	6.7'
8	19.2	8.9'
10	123	11 1′

LUMINANCE (Average cd/m²)

Average 0°		
Degrees	Luminance	
45	19726	
55	7703	
65	2135	
75	0	
85	0	

Fixtures tested to IES recommended standard for solid state lighting per LM-79-08. Photometric performance on a single unit represents a baseline of performance for the fixture. Results may vary in the field.