



circuit breaker 3VA4 UL Frame 125 breaking capacity class M 35 kA @ 480 V 3-pole, line protection TM210, FTFM, $I_n=30$ A overload protection $I_r=30$ A permanently set short-circuit protection $I_i=10 \times I_n$ terminal connection

| Model | |
|--|--|
| product brand name | SENTRON |
| product designation | Molded-case circuit breaker |
| product designation / according to UL file | MEAB |
| design of the product | System protection |
| design of the load switch / according to UL 489 / Heating, Air Conditioning, and Refrigeration circuit breaker (HACR Type) | Yes |
| design of the load switch / according to UL 489 / High-Intensity-Discharge circuit breaker (HID Type) | Yes |
| design of the load switch / according to UL 489 / Switching Duty circuit breaker (SWD Type) | No |
| design of the overcurrent release | TM210 |
| protection function of the overcurrent release | LI |
| number of poles | 3 |
| General technical data | |
| operating voltage / at AC / rated value | 690 V |
| power loss [W] / maximum | 9 W |
| power loss [W] / for rated value of the current / at AC / in hot operating state / per pole | 3 W |
| mechanical service life (operating cycles) / typical | 15 000 |
| electrical endurance (operating cycles) / at 480 V | 8 000 |
| electrical endurance (operating cycles) / at 600 V | 4 000 |
| product feature / for neutral conductors / upgradable/retrofitable / short-circuit and overload proof | No |
| ground-fault monitoring version | Without |
| product function | |
| • communication function | No |
| • other measurement function | No |
| Net Weight | 0.743 kg |
| Current | |
| marking / according to UL 489 / 100%-rated breaker | No |
| operational current | |
| • at 40 °C | 30 A |
| • at 45 °C | 29 A |
| • at 50 °C | 29 A |
| • at 55 °C | 28 A |
| • at 60 °C | 27 A |
| • at 65 °C | 27 A |
| • at 70 °C | 26 A |
| Switching capacity according to IEC 60947 | |
| switching capacity class of the circuit breaker | M |
| design of short-circuit protection | For switching power values in DC networks, see the 3VA molded case circuit |

breaker device manual; link to be found under Service & Support in the last chapter

Switching capacity according to UL 489

| | |
|--|----------------------------------|
| current breaking capacity | |
| <ul style="list-style-type: none"> at 240 V at 480 Y/277 V at 480 V at 600 Y/347 V | 85 kA 35 kA 35 kA 18 kA |

Adjustable parameters

| | |
|--|------------|
| adjustable response value delay time (tr) / for L-tripping / with I2t characteristic | |
| <ul style="list-style-type: none"> minimum maximum | 1 s 1 s |
| product function / grounding protection | No |

Mechanical Design

| | |
|---|----------------------|
| product component | |
| <ul style="list-style-type: none"> undervoltage release voltage trigger trip indicator | No No No |
| height [in] | 5.09 in |
| height | 129.4 mm |
| width [in] | 3 in |
| type of connectable conductor cross-sections / of the round conductor terminal / stranded | 1 x (14 AWG - 8 AWG) |
| width | 76.2 mm |
| depth [in] | 2.96 in |
| depth | 75.1 mm |

Connections

| | |
|---|--|
| arrangement of electrical connectors / for main current circuit | output side: circular conductor connection |
| type of electrical connection / for main current circuit | Infeed side: Low tab |
| design of the surface / of the connections / on the bottom of the switch (N, 2, 4, 6) | Tin |

Auxiliary circuit

| | |
|--|---|
| number of CO contacts / for auxiliary contacts | 0 |
|--|---|

Accessories

| | |
|--|----|
| product extension / optional / motor drive | No |
|--|----|

Environmental conditions

| | |
|--|------------------------------------|
| protection class IP / on the front | IP40 |
| ambient temperature | |
| <ul style="list-style-type: none"> during operation / minimum during operation / maximum during storage / minimum during storage / maximum | -25 °C 70 °C -40 °C 80 °C |

Approvals / Certificates

| | | |
|--------------------------|-----|-------|
| General Product Approval | EMV | other |
|--------------------------|-----|-------|



[Miscellaneous](#)



[Miscellaneous](#)

| | |
|-------|-------------|
| other | Environment |
|-------|-------------|

[Confirmation](#)

[Miscellaneous](#)

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

[Information- and Downloadcenter \(Catalogs, Brochures,...\)](#)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA4130-5ED34-0AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA4130-5ED34-0AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA4130-5ED34-0AA0

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





