

Series Spec Sheet

L2STR

LED STRIP

3 CCT and 3 Power Selectable Optional Emergency Remote

The L2STR series of versatile LED strips are designed to deliver efficient and high impact illumination. These luminaires feature a rounded lens that evenly diffuses the light and an innovative housing built for quick and easy installation. Whether for retrofit or new construction, the L2STR series is the ideal choice for a variety of commercial and industrial applications.

FEATURES AND SPECIFICATIONS

• Construction

Physical Characteristics

- Sleek two-part housing design with tool-less entry
- Safety cables placed between lens compartment and housing for easy installation and maintenance
- CCT and Power Selectable switches are placed discretely inside the housing
- 24 gauge white powder painted steel
- Frosted PMMA lens

Mounting

- Surface, suspended or row mounted (see accessories)
- V-Hooks and canopy plate for octagonal junction box are included

• Performance Data

- Available in 3 500/4 000/5 000 K selectable color temperature
- 80+ CRI
- Electrical ratings: 120-347 V
- Estimated life of over 156 000 hours to L70
- 0-10 V dimming standard with 12 V auxiliary output
- 2.5 kV surge protection
- Operating temperature:
 - 20 °C to 50 °C (-4 °F to 122 °F)
- Operating temperature with LINK or Emergency battery backup:
 - 20 °C to 25 °C (-4 °F to 77 °F)

• Optional Emergency Lighting

LINK Normally ON Emergency Remote LED Strip

- Consuming 11 W, 12 - 24 VDC
- 200 mA constant current
- Delivers 1 222 - 1 344 lumens in emergency mode
- Ease of maintenance when used with Stanpro emergency lighting battery units complete with auto test function
- Complements Stanpro's normally ON LED strip family
- Patent pending

Please view the LINK specification section for more details on this technology

• Emergency Lighting Compliances

- CSA certified as a C22.2 C141-15 emergency lighting luminaire
- Meets ICES-005 requirements

• General Lighting Compliances

- cULus listed for damp locations
- DLC Premium and Standard
- Meets requirements of ICES-005 issue 5 class A for use in commercial applications



OVERVIEW

Light source	LED
Watts (W)	20, 56
	18/25/30
	25/30/40
	34/38/45
	65/75/90
Lumen output (lm)	2 520 - 12 780
Efficacy (lm/W)	131 - 155
Color temperature (K)	3 500/4 000/5 000
CRI	80+

¹ 5 year warranty for the LINK module.

Not all products are qualified on the DLC QPL. To view our DLC qualified products, please consult the DLC Qualified Products List at www.designlights.org/search.

QUICK SHIP AND TECHNICAL SPECIFICATION TABLE

Order code	Model number	Watts	Volts	Color temp.	Lumen output	Efficacy	CRI	Life L70	Tested hours LM-80	Dimming	Power factor	THD	Master case qty
		(W)	(V AC)	(K) ¹	(lm)	(lm/W)		(hrs) ⁴	(hrs) ⁴	(Yes/No)		(%)	
24" CCT Selectable													
69390	L2STR-24LS1-Q/3C	20	120-347	3 500/4 000/5 000	2 640 ²	132	80+	156 000	10 000	Yes	0.90	10	6
36" CCT and Power Selectable													
69583	L2STR-36LP30-Q/3C	18/25/30	120-347	3 500/4 000/5 000	2 700/3 650/ 4260 ³	132	80+	156 000	10 000	Yes	0.90	10	6
48" CCT and Power Selectable													
69391	L2STR-48LP40-Q/3C	25/30/40	120-347	3 500/4 000/5 000	3 875/4 500/5 680 ³	132	80+	156 000	10 000	Yes	0.90	10	6
69392	L2STR-48LP45-Q/3C	34/38/45	120-347	3 500/4 000/5 000	5 270/5 776/6 660 ³	138	80+	156 000	10 000	Yes	0.90	10	6
48" CCT Selectable													
69393	L2STR-48LS2-Q/3C	56	120-347	3 500/4 000/5 000	7 392 ²	132	80+	156 000	10 000	Yes	0.90	10	6
96" CCT and Power Selectable													
69394	L2STR-96LP90-Q/3C	65/75/90	120-347	3 500/4 000/5 000	9 750/11 100/12 780 ³	135	80+	156 000	10 000	Yes	0.90	10	1

¹ Typical color temperature range: +/- 5 %.

² Lumen values are derived from DLC reported data at 3 500 K. Please refer to the LUMEN SPECIFICATION TABLE for more details on other color temperatures.

³ Lumen values are based on 4 000 K default programming. Please refer to the LUMEN SPECIFICATION TABLE for more details on other color temperatures.

⁴ Life hours are derived from IESNA LM-80-08 testing report and projected per IESNA TM-21-11 extrapolations.

DLC UNIQUE ID TABLE

Order Code	Model Number	DLC Premium Unique ID ¹	DLC Standard Unique ID ²
69390	L2STR-24LS1-Q/3C	S-9ZPAM0	S-NCPTJ8
69583	L2STR-36LP30-Q/3C	S-EX5SG1	S-CXRFZ0
69391	L2STR-48LP40-Q/3C	S-HQVFW6	S-68UP5A
69392	L2STR-48LP45-Q/3C	S-KQLIU1	S-ICD3NR
69393	L2STR-48LS2-Q/3C	S-7WWDJM	S-43XGPW
69394	L2STR-96LP90-Q/3C	S-5FR32B	S-52TLY8

¹ Primary Use Designation: Stairwell And Passageway Luminaires

² Primary Use Designation: Direct Linear Ambient Luminaires

LUMEN SPECIFICATION TABLE

Order code	Model number	Watts (W)	3 500 K		4 000 K		5 000 K	
			Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)
69390	L2STR-24LS1-Q/3C	20	2 640	132	2 800	140	2 640	132
69583	L2STR-36LP30-Q/3C	18	2 520	140	2 700	150	2 556	142
		25	3 400	136	3 650	146	3 450	138
		30	3 960	132	4 260	142	4 020	134
69391	L2STR-48LP40-Q/3C	25	3 625	151	3 875	155	3 675	147
		30	4 200	140	4 500	150	4 260	142
		40	5 280	132	5 680	142	5 360	134
69392	L2STR-48LP45-Q/3C	34	4 930	145	5 270	155	4 998	147
		38	5 396	142	5 776	152	5 472	144
		45	6 210	138	6 660	148	6 300	140
69393	L2STR-48LS2-Q/3C	56	7 392	132	7 784	139	7 336	131
69394	L2STR-96LP90-Q/3C	65	9 100	140	9 750	150	9 230	142
		75	10 350	138	11 100	148	10 500	140
		90	12 150	135	12 780	142	12 060	134

DEFAULT PROGRAMMING

69390: 4 000 K

69583: 30 W / 4 000 K

69391: 40 W / 4 000 K

69392: 45 W / 4 000 K

69393: 4 000 K

69394: 75 W / 4 000 K

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

ORDERING GUIDE

Series	Size	Lamp type	Lumen package (W) ¹	Volts (V AC)	Color temp. (K)	Options
L2STR	24 - 24"	L- LED	S1 - 20	Q - 120-347 W - 120-277 ²	3C - 3 500/4 000/5 000	EL - LINK Normally ON emergency remote ^{3,4} DL - 8 W Emergency battery backup (120-277 V only) ⁵
	48 - 48"		P40 - 25/30/40 P45 - 34/38/45 S2 - 56			
	96 - 96"		P90 - 65/75/90			

¹ See IES files or LUMEN SPECIFICATION TABLE for details.

² Only available for 48" and 96" luminaires when used with DL option.

³ When in Emergency Model with EL option, half of the 96" luminaire will remain illuminated.

⁴ When in Emergency Mode with EL option, luminaire only consumes 11 W.

For emergency lighting spacing with EL option, please see page 7.

⁵ Only available for 48" and 96" luminaires in 120-277 V.

LINK TECHNICAL SPECIFICATION TABLE

Size	Lumen package	Watts (W)	LINK Watts (W)	LINK Lumen output (lm)
24"	LS1	20	11	1 257
48"	LP40	25		1 294
		30		1 291
		40		1 222
	LP45	34		1 344
		38		1 322
		45		1 268
96"	LP90	56		1 223
		65		1 295
		75		1 241
		90		1 242

EMERGENCY BATTERY BACKUP SPECIFICATION TABLE

Size	Lumen package	Watts (W)	Emergency battery backup Watts (W)	Emergency battery backup Lumen output (lm)
48"	LP40	25	8	1 035
		30		1 033
		40		978
	LP45	34		1 075
		38		1 057
		45		1 014
96"	LP90	56		965
		65		1 036
		75		993
		90		994



Standard placement of the test switch and indicator light is on the end cap of the luminaire. For alternative placement, please contact your Stanpro customer service representative.

Discharge Time (min.)	≥ 90
Recharge Time (hrs)	≥ 24

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

ACCESSORIES (order separately)

Order code	Type
68676	Suspension kit - 2 chains (1 m)
69082	10' Aviation cable kit with canopy, power cord & dimming wires
69405	Continuous row mounting connector
69398	Transparent end caps (set of 2)
69412	Wire guard kit 24"
69413	Wire guard kit 48"
69395	Replacement lens 24"
69585	Replacement lens 36"
69396	Replacement lens 48"
69397	Replacement lens 96"


¹ For 96" luminaires, order 2 units.

INCLUDED IN THE BOX



TRANSPARENT END CAPS

Our transparent end caps accessory is the perfect option for creating a seamless and consistent run of light when the L2STR LED strips are mounted in a continuous row. This accessory can also be used for regular installations (non-row mounted) to create a unique and pleasant 360° illumination!



COMPATIBLE DIMMERS¹

Brand	Model
Leviton	IlumaTech IP710-LFZ DS710
Lutron	Maestro MS-Z101 Nova T NTSTV DIVA DVSTV
Legrand	RH4FBL3PW
Philips	Sunrise SR1200ZTUNV


Dimming range: 0%-100%

¹ This table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Some dimmers may require more than one product for stable operation. Stanpro recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation.


Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

DIMENSIONS AND WEIGHT


24"




36"



48"



96"



	24"	36"	48"	96"
Net weight (lbs)	2.6	3.5	4.4	8.5

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

LINK


NORMALLY ON EMERGENCY REMOTE LUMINAIRE

This luminaire can be used with an emergency backup powered by either a 12 V or 24 V DC Stanpro battery unit, complete with or without auto test.

NORMAL MODE



EMERGENCY MODE



TYPICAL SPECIFICATION

Supply and install Stanpro LINK _____ ft, LED strip, Model number: _____ remote normally ON emergency luminaire, CSA C22.2 141-15 certified and meet the requirements prescribed by ICES-005. Normally ON when AC is present and when connected to a Stanpro battery unit complete with or without auto test, this luminaire shall act as an emergency lighting remote and consume 11 W of DC power in _____ V producing 1 222 - 1 344 lumens in emergency mode.

The remote normally ON emergency luminaire shall be powered by a Stanpro emergency lighting battery unit as described herein and shown on the drawings. The Stanpro auto diagnostic micro-controller board shall supply the rated load for a minimum of a 1/2 hour to 87.5% of the rated battery voltage. The unit shall be rated 120 V, 277 V or 347 V, 60 Hz and be CSA listed. The unit shall have an output of: ___V and ___W. The charge voltage factory set to $\pm 1\%$ tolerance. High efficiency, rapid recovery, precision control charging system shall be employed to promote long battery life and reduce the potential for grid corrosion. The charger shall provide a continuous high charge to recharge the battery, when the battery is at full capacity, the charger will shut-off. Periodically the charger shall provide a pulse of energy to keep the battery topped off. The pulse charger shall be precisely regulated and shall charge the battery in relation to its temperature, state or charge and input voltage fluctuations. The charger shall be current limited, temperature compensated, short-circuit proof and reverse polarity protected. The unit shall be furnished with an electronic lockout circuit, which will connect the battery when the AC circuit is activated, and an electronic brownout circuit, which will activate the emergency lights when utility power dips below 75% of nominal voltage. A low voltage battery protection circuit shall be provided and will disconnect the load when the battery reaches the end of discharge.

The automated testing performed by the Stanpro auto test system has been designed to comply with all of the requirements of the National Fire Code. Every month a 5 minute discharge and diagnostic test checks the operational status of the unit. Every 12 months, this test is extended to the full 30 minute, code required duration. This ensures that the battery charger is recharging the battery in accordance with code requirements.


The unit shall be Stanpro model: SL_____

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

LINK

NORMALLY ON EMERGENCY REMOTE LUMINAIRE

LINK Wiring Diagram



LEGEND

- AC wires
- Connected to the dedicated lighting circuit
- DC wires
- LINK factory installed


Emergency mode	Spacing
L2STR	Average spacing for 1 out of every 4 luminaires, normally ON in the path of egress, when at 8, 10, or 12 foot mounting heights.

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

PHOTOMETRIC DATA¹

69390 • L2STR-24LS1-Q/3C • 4 000 K • 2 798.0 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	619.8	22.1%
0-40	1 014.3	36.3%
0-60	1 810.2	64.7%
60-90	721.4	25.8%
70-100	506.4	18.1%
90-120	215.5	7.7%
0-90	2 531.6	90.5%
90-180	266.4	9.5%
0-180	2 798.0	100%


Illuminance at a distance

Center beam fc	Beam width
1.7'	4.1' 7.8'
3.3'	8.0' 15.1'
5.0'	12.2' 22.9'
6.7'	16.3' 30.7'
8.3'	20.2' 38.1'
10.0'	24.3' 45.9'

■ Vert. spread: 101.2°
■ Horiz. spread: 132.9°

69583 • L2STR-36LP30-Q/3C • 30 W • 4 000K • 4 256.2 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	976.0	22.9%
0-40	1 598.3	37.6%
0-60	2 859.3	67.2%
60-90	1 018.8	23.9%
70-100	604.9	14.2%
90-120	245.2	5.8%
0-90	3 878.2	91.1%
90-180	378.0	8.9%
0-180	4 256.2	100%


Illuminance at a distance

Center beam fc	Beam width
1.7'	4.5' 6.7'
3.3'	8.7' 12.9'
5.0'	13.2' 19.6'
6.7'	17.7' 26.3'
8.3'	22.0' 32.6'
10.0'	26.5' 39.2'

■ Vert. spread: 105.8°
■ Horiz. spread: 126.0°

69391 • L2STR-48LP40-Q/3C • 40 W • 4 000 K • 5 675.6 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	1 243.7	21.9%
0-40	2 036.9	35.9%
0-60	3 642.1	64.2%
60-90	1 469.0	25.9%
70-100	1 036.0	18.3%
90-120	448.9	7.9%
0-90	5 111.1	90.1%
90-180	564.5	9.9%
0-180	5 675.6	100%

Illuminance at a distance

Center beam fc	Beam width
1.7'	4.2' 7.9'
3.3'	8.1' 15.3'
5.0'	12.3' 23.3'
6.7'	16.4' 31.2'
8.3'	20.3' 38.6'
10.0'	24.5' 46.5'

■ Vert. spread: 101.5°
■ Horiz. spread: 133.5°


¹ Complete IES files available on our website.

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

PHOTOMETRIC DATA¹

69392 • L2STR-48LP45-Q/3C • 45 W • 4 000 K • 6 655.0 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	1 452.3	21.8%
0-40	2 378.0	35.7%
0-60	4 253.5	63.9%
60-90	1 725.2	25.9%
70-100	1 221.8	18.4%
90-120	536.0	8.1%
0-90	5 978.7	89.8%
90-180	676.3	10.2%
0-180	6 655.0	100%


Illuminance at a distance

Center beam fc	Beam width
1.7'	4.2' 7.9'
3.3'	8.1' 15.4'
5.0'	12.3' 23.3'
6.7'	16.5' 31.2'
8.3'	20.5' 38.6'
10.0'	24.7' 46.6'

Vert. spread: 101.9°
Horiz. spread: 133.5°

69393 • L2STR-48LS2-Q/3C • 4 000 K • 7 778.3 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	1 697.9	21.8%
0-40	2 781.2	35.8%
0-60	4 976.0	64%
60-90	2 015.4	25.9%
70-100	1 425.7	18.3%
90-120	623.6	8%
0-90	6 991.3	89.9%
90-180	786.9	10.1%
0-180	7 778.3	100%


Illuminance at a distance

Center beam fc	Beam width
1.7'	4.2' 8.0'
3.3'	8.1' 15.5'
5.0'	12.3' 23.5'
6.7'	16.4' 31.5'
8.3'	20.4' 39.0'
10.0'	24.5' 47.0'

Vert. spread: 101.7°
Horiz. spread: 133.9°

69394 • L2STR-96LP90-Q/3C • 90 W • 4 000 K • 12 770.5 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	2 786.8	21.8%
0-40	4 563.1	35.7%
0-60	8 162.1	63.9%
60-90	3 310.5	25.9%
70-100	2 344.6	18.4%
90-120	1 028.6	8.1%
0-90	11 472.6	89.8%
90-180	1 297.9	10.2%
0-180	12 770.5	100%

Illuminance at a distance

Center beam fc	Beam width
1.7'	4.2' 7.9'
3.3'	8.1' 15.4'
5.0'	12.3' 23.3'
6.7'	16.5' 31.2'
8.3'	20.5' 38.6'
10.0'	24.7' 46.6'

Vert. spread: 101.9°
Horiz. spread: 133.5°

¹ Complete IES files available on our website.

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.