

2024 Specification Sheet - English

**LONG DESCRIPTION –**

Long Description Marketing Copy

Double layered vinyl handles for comfort and slip resistance. Reduced handle size allows for easy storage of tools in pouches and tool bags. High leverage design provides 46% greater cutting and gripping power than standard plier designs. Forged from chrome vanadium steel for greater strength and long life of the whole plier

PRODUCT NAME –

Page Title

9" Dipped Grip High-Leverage Side-Cutting Pliers

PRODUCT OVERVIEW –

Marketing Text 1

Double layered vinyl handles for comfort and slip resistance

Marketing Text 2

Reduced handle size allows for easy storage of tools in pouches and tool bags

Marketing Text 3

High leverage design provides 46% greater cutting and gripping power than standard plier designs

Marketing Text 4

Forged from chrome vanadium steel for greater strength and long life of the whole plier

Marketing Text 5

Laser hardened cutting knives keep edge and last longer than induction hardened knives

Marketing Text 6

Designed to provide long life even when cutting hardened wire, ACSR, screws, bolts and nails

Marketing Text 7

Tempered handles help to absorb the "snap" and reduce fatigue when cutting through hardened wire, bolts and screws

Marketing Text 8

Diamond serrated jaws for superior gripping power

Marketing Text 9

Exceeds ASME/ANSI specifications

Marketing Text 10

Note: This is not an insulated tool

Marketing Text 11

Lifetime limited warranty

PRODUCT SPECIFICATION –

Product Specification 1

Grip Length : 9.000 IN

Product Specification 2

Grip Type : Dipped

Product Specification 3

Handle Type : Double Layered Vinyl

Product Specification 4

Material : Chrome Vanadium Steel

Product Specification 5

Overall Length : 9-3/8 IN (23.800 CM)

Product Specification 6

Standard : ASME/ANSI

Product Specification 7

Type : High Leverage

Product Specification 8

Weight : 1.130 LB (0.510 KG)