

2024 Specification Sheet - English

**LONG DESCRIPTION –**

Long Description Marketing Copy

Heavy-Duty Construction For Longer Life. Handle Marked For Easy Identification Of Screwdriver Size, Type And Length. Precision-Machined Tips For Accurate Fastener Contact. Strong, Durable Black Phosphate Tips Prevent Chipping of Plating

PRODUCT NAME –

Page Title

Screwdriver Set, 7 Piece

PRODUCT OVERVIEW –

Marketing Text 1

Heavy-Duty Construction For Longer Life

Marketing Text 2

Handle Marked For Easy Identification Of Screwdriver Size, Type And Length

Marketing Text 3

Precision-Machined Tips For Accurate Fastener Contact

Marketing Text 4

Strong, Durable Black Phosphate Tips Prevent Chipping of Plating

Marketing Text 5

High-Grade, Rust Resistant, Chrome-Plated Finish

Marketing Text 6

Soft, Cushioned Grip For Extra Comfort And Torque

Marketing Text 7

Our general purpose tools exceed ASME/ANSI Specifications

Marketing Text 8

Lifetime Limited Warranty

Marketing Text 9

Note: This is not an insulated tool

PRODUCT SPECIFICATION –

Product Specification 1

Blade Finish : Chrome-Plated Shank, Durable Black Phosphate Tip

Product Specification 2

Contains : 3/16 IN X 4.00 IN Cabinet, 3/16 IN X 6.000 IN Cabinet, 1/4 IN X 4.000 IN Keystone, 1/4 IN X 4.000 IN Cabinet, 5/16 IN X 6.000 IN Keystone, #1 X 3.000 IN Phillips And #2 X 4.000 IN Phillips

Product Specification 3

Handle Type : Soft, Cushioned Grip

Product Specification 4

Number Of Pieces : 7

Product Specification 5

Standard : ASME/ANSI

Product Specification 6

Weight : 1.630 LB (0.740 KG)