

Project: \_\_\_\_\_ Type: \_\_\_\_\_

Drawn by: \_\_\_\_\_ Catalogue #: \_\_\_\_\_ Date: \_\_\_\_\_

*Individual Spec Sheet*

# LED HIGH INTENSITY FILAMENT LAMP

## ORDERING INFORMATION

**Order code:** 69599  
**Model number:** ED28/40W/40K/BYP/EX39/V/FIL/ND/STD  
**UPC:** 069549028128  
**Case quantity:** 12

## PHYSICAL DATA

**Base:** EX39  
**Shape:** ED28


## PERFORMANCE DATA

**Watts (W):** 40  
**Traditional equivalent (W)** 250  
**Volts (VAC):** 120-277  
**Color temperature (K)1:** 4 000  
**Lumen output (lm)2:** 7 500  
**Efficacy (lm/W):** 188  
**CRI:** 80  
**Life L70 (h)3:** 25 000  
**Beam angle (°):** Universal  
**Power factor:** >0.9  
**Frequency (Hz):** 50/60  
**Operating temp. range:** Open Fixture: -30 °C to 50 °C (-22 °F to 122 °F)  
 Enclosed Fixture: -30 °C to 45 °C (-22 °F to 113 °F)  
 Indoor and Outdoor

### Application (Indoor/Outdoor):

<sup>1</sup> Typical color temperature range: +/- 5 %.  
<sup>2</sup> Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.  
<sup>3</sup> Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations.

## DIMENSIONS



This lighting equipment meets requirements of ICES-005 issue 5 class B for use in residential applications. Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.