

Project: _	
Drawn by	

Drawn by:

Individual Spec Sheet LED REFLECTORS

MR16 - GU10

5 CCT Selectable

ORDERING INFORMATION

Order code:	69626
Model number:	GU10/6.5W/50
UPC:	06954902838
Case quantity:	100

PHYSICAL DATA

Shape:MR16Base:GU10Heat sink color:White

PERFORMANCE DATA

Watts (W):	6.5
Volts (VAC):	120
Colour temperature (K) ¹ :	2 7000/3 000/3 500/4 000/5 000
Lumen output (Im) ² :	500
Efficacy (Im/W):	77
CRI:	80
Life L70 (h) ³ :	25 000
Dimming:	Phase cut
Beam angle (°):	40
Power factor:	> 0.70
Frequency (Hz):	60
Operating temp. range:	-30 °C to 40 °C / -22 °F to 104 °F
1 Typical colour temperature range; +/- 5 %.	

2 Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.
3 Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations.

LUMEN SPECIFICATION TABLE

2 700 K		3 00	00 K	3 50	00 K	4 00	00 K	5 00	00 K
Lumen output (Im)	Efficacy (Im/W)								
591	91	571	88	572	88	537	83	529	81

DEFAULT PROGRAMMING

2 700 K


COMPATIBLE DIMMERS¹

Brand	Model
LUTRON	DVCL-153P, DVCL-253P, AYCL-253P, DVELV-300P, SELV-300P, MACL-153P
COOPER	DAL06P, SAL06P3
LEVITON	6615, 6674, IPL06, DDMX1, DSL06-1LZ, DSM10-1LZ, IPE04-1LZ
LEGRAND	RH703PTUTC

¹ This table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unjue, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Some dimmers may require more than one product. Of estable operation. Standard recommends to use dimmers disgined to work with LED products. Older dimmers designed for incandescent products may cause erratic operation.

DIMENSIONS

2" (50 mm)



Type: ______ Date: _____









_____ Catalogue #: ___

