

Project: \_\_\_\_\_ Type: \_\_\_\_\_

Drawn by: \_\_\_\_\_ Catalogue #: \_\_\_\_\_ Date: \_\_\_\_\_

## Individual Spec Sheet

# VTE4-L GEN. 2 LED VAPOR TIGHT

### ORDERING INFORMATION

**Order code:** 69595  
**Model number:** VTE4-LS4B-Q-3C  
**UPC:** 069549028081  
**Case quantity:** 6  
**DLC Unique ID:** 6 S-XFTL18 (DLC Premium) / S-RJ5MKU (DLC Standard)

### PHYSICAL DATA

**Size in. (cm):** 50 1/4" x 6 1/2" x 3 3/4" (127.6 x 16.5 x 9.5 cm)  
**Lens material:** UV stabilized polycarbonate frosted lens  
**Latch material:** Stainless steel  
**Housing material:** Polycarbonate  
**Mounting:** Wall, ceiling or suspended

### PERFORMANCE DATA

**Watts (W):** 60 W  
**Volts (V AC):** 120-347  
**Color temperature (K)<sup>1</sup>:** 3CCT (3 500/4 000/5 000 K)  
**Lumen output (lm)<sup>2,3</sup>:** 8 441  
**Efficacy (lm/W):** 141  
**CRI:** 80+  
**Life L70 (hrs)<sup>4</sup>:** 135 000  
**Tested LM-80 (hrs)<sup>4</sup>:** 9 000  
**Dimming:** 0-10 V  
**Power factor:** > 0.90  
**THD (%):** < 20  
**Frequency (Hz):** 60  
**Surge protection (kV):** 2.0  
**Operating temp. range:** -40°C to +40°C (-40°F to 104°F)

<sup>1</sup> Typical colour temperature range: +/- 5 %

<sup>2</sup> Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %

<sup>3</sup> Lumen values are based on 4 000 K default programming. Please refer to the LUMEN SPECIFICATION TABLE for more details on other color temperatures.

<sup>4</sup> Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations.

### LUMEN SPECIFICATION TABLE

Order code	3 500 K		4 000 K		5 000 K	
	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)
69595	8 069	33	8 441	141	8 281	137



ICES  
005



Not all products are qualified on the DLC QPL. To view our DLC qualified products, please consult the DLC Qualified Products List at [www.designlights.org/search](http://www.designlights.org/search).


**COMPATIBLE DIMMERS<sup>1</sup>**

Brand	Model
LUTRON	DVSTV-HX DIVA 8 AMP 3-WAY/SINGLE -POLE 0-10V DIMMER
EATON	Controls DF10P-CI DECORATOR 0-10V DIMMER
COOPER	SF10P-W
LUXDRIVE	DIMMING CONTROL - 0-10V LOW VOLTAGE WALL MOUNT CONTROL
LUTRON	DVTW-WH DIVA 30mA SINGLE POLE 0-10V FLUORESCENT DIMMER
LEVITON	DS710-10Z

Dimming range: 10%-100%

<sup>1</sup> This table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Some dimmers may require more than one product for stable operation. Stanpro recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation.


**DIMENSIONS**



**PHOTOMETRIC DATA<sup>1</sup>**

**69595 • VTE4-LS4B-Q-3C • 4 000 K • 8 433 LM**

**Polar candela distribution**



**Zonal lumen summary**

Zone	Lumens	% Luminaire
0-30	2 059.2	24.4
0-40	3 349.9	39.7
0-60	5 895.3	69.9
60-90	2 042.4	24.2
70-100	1 273.4	15.1
90-120	393.5	4.7
0-90	7 937.8	94.1
90-180	495.4	5.9
0-180	8 433.2	100

**Illuminance at a distance**

Center beam fc	Beam width
1.7'	929
3.3'	247
5.0'	107
6.7'	59.8
8.3'	39.0
10.0'	26.9

Beam width	Beam width
5.5'	4.4'
10.8'	8.6'
16.3'	13.0'
21.9'	17.5'
27.1'	21.7'
32.6'	26.1'

Vert. spread: 117.0°  
Horiz. spread: 105.1°

<sup>1</sup> Complete IES files available on our website.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: \_\_\_\_\_  
 Company: \_\_\_\_\_  
 Signature: \_\_\_\_\_

Date: \_\_\_\_\_

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.